


## Offset Pipe Clamp Fig. 103



**Size Range:** ¾" through 8"

**Material:** Carbon Steel (Available in stainless steel upon request)


**Finish:** Plain or Hot-Dip Galvanized with Zinc Plated Fasteners

**Service:** For use in supporting piping away from wall or floor.

**Maximum Temperature:**  
Plain 650° F, Galvanized 450° F

**Ordering:** Specify pipe size, figure number, name and finish.

**Service:** For use in supporting horizontal piping away from the wall or floor (not to be used as a riser type support).



**Fig. 103: Dimensions (in) • Loads (lbs) • Weight (lbs)**

Pipe Size	Max Load	Weight	W	B	D	Bolt Dia. F	G Width
¾	190	1.50	8¾	2½	7/16	¾	1¼
1		1.60	9¼	2⅝			
1¼		1.70	9¾	2 <sup>13</sup> / <sub>16</sub>			
1½		1.80	10	2 <sup>15</sup> / <sub>16</sub>			
2	420	2.70	11¼	3 <sup>3</sup> / <sub>16</sub>	9/16	½	1½
2½		2.90	11¾	3 <sup>7</sup> / <sub>16</sub>			
3		3.20	12 <sup>7</sup> / <sub>8</sub>	3¾			
4		4.60	13 <sup>7</sup> / <sub>8</sub>	4¼			
5	610	7.30	15 <sup>5</sup> / <sub>8</sub>	4¾	11/16	5/8	2
6		7.80	16¾	5 <sup>5</sup> / <sub>16</sub>			
8		9.00	18¾	6 <sup>5</sup> / <sub>16</sub>			

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	