## **Pipe Hangers & Supports**



One-Hole Clamp **Fig. 126** 



Size Range: 3/8" through 4"

Material: Malleable Iron

Figire Phase or 7:00 Plane

Finish: Plain or Zinc Plated

(Available in  $\frac{3}{8}$ " - 3")

Service: For support of standard conduit, cable and steel pipe on walls or sides of beams. Not recommended for use horizontally on ceilings, bottoms of beams and similar installations since the factor of safety is greatly reduced when so used.

Maximum Temperature: 450° F

Ordering: Specify pipe size, figure number, name and finish. Specify nominal size of conduit or pipe or outside diameter of lead cable with which the clamp is to be used.



Fig.	. 126: Di	imensions (	(in)	<ul><li>Loads (</li></ul>	lbs	) • Wei	ght (	(lbs)
------	-----------	-------------	------	---------------------------	-----	---------	-------	-------

Pipe Size	Cable Size or Outside Dia. of Conduit ■	Weight	Dia. of Hole - A	Size Screw/Bolt	
<sup>3</sup> / <sub>8</sub>	0.67	0.03	1/4	No. 10	
1/2	0.84	0.03			
3/4	1.05	0.05	5/16	1/4	
1	1.31	0.09		74	
11/4	1.66	0.12	3/8		
11//2	1.90	0.16	7/	3/	
2	2.37	0.25	7/16	3/8	
21/2	2.87	0.49	11/		
3	3.50	0.82	<sup>11</sup> / <sub>16</sub>	5/8	
4	4.50	1.30	3/4		

## ■ Screws or bolts not included

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	