


Plastic Coated U-Bolts





Size Range: 1/2" through 8"

Material: Carbon steel U-bolt and four finished hex nuts. Formed portion of the U-bolt is plastic coated.

Maximum Temperature: 225° F

Service: Recommended for support or guide for glass, copper, brass and aluminum pipe.

Approvals: Complies with Federal Specification A-A-1192A (Type 24), WW-H-171-E (Type 24), ANSI/MSS SP-69 and MSS SP-58 (Type 24).

Ordering: Specify pipe size x rod size (e.g., 2 x 3/8), figure number and name. If hex nuts are not required, specify "without hex nuts".



Fig. 137C: D	imensions	(in) •	Loads (l	lbs) • We	ight (lbs)
--------------	-----------	--------	----------	-----------	------------

Pipe Size	Rod Size A	Max Load	Weight	В	C	D	E	F
1/2	1/4	580	0.11	¹⁵ / ₁₆	13/16	2³/ ₄	2⅓8	25/16
3/4			0.12	111//8	13//8			27/32
1			0.12	13//8	15/8			23/32
111/4	3/8	1,460	0.28	111/16	21/16	27/8		21/32
11//2			0.30	2	23/8	3	21//2	21/16
2			0.33	27/16	213/16	31/4		
21/2	1/2	2,700	0.73	215/16	37/16	33/4	3	25/16
3			0.78	39/16	41/16	4		
31/2			0.84	41/16	49/16	41/4		21/4
4			0.90	49/16	51/16	41/2		
5			1.00	55/8	61//8	5		27/32
6	5/ ₈	4,320	2.00	63/4	73/8	61//8	31//2	2 ¹³ / ₁₆
8			2.30	83/4	93/8	71/8		

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	