

One Hole Pipe Strap Fig. 185 (Formerly Afcon Fig. 513)

Size Range: 3/4" through 2" Material: Carbon Steel

Finish: Pre-Galvanized per ASTM A653

Service: Hanger for CPVC pipe in the horizontal position on the side of structural wood beams and Steel 20 Ga. (min) with hanger tab in the upward position only (Fig. A). It can also be used as a guide to limit movement of vertical CPVC pipe with the tab in the horizontal position.

Approvals: UL and ULC Listed.


Installation:

- · Place hanger over pipe.
- · Secure hanger to mounting surface with screws provided.
- Steel applications require one (1) #14 x 1" hex washer head self-drilling TEK screw. Not Supplied. Part Number STD-0090.


Features:

- Beveled edge design helps protect the CPVC pipe from any rough surface.
- Easily attaches to wood structure with #10 x 1" hex washer head self threading screw supplied with product. No pre-drilling required.

Ordering: Specify CPVC pipe size, figure number and description.










Fig. 185: Dimensions (in) • Weight (lbs,
--------------------------------------	------

CPVC Pipe Size	A	В	øС	E	F	Max. Hanger Spacing (ft)	Approx. Weight/100 (lbs)
3/4	17/16	21/2	1/4	111/8	111/4	51/2	8
1	13/4	27/8	1/4	111/8	11//2	6	9
11/4	111/16	3	1/4	11//8	17//8	61/2	10
111/2	17//8	37/16	1/4	11//8	21//8	7	12
2	2	37/8	1/4	111//8	25/8	8	14

PROJECT INFORMATION	APPROVAL STAMP			
Project:	Approved			
Address:	Approved as noted			
Contractor:	Not approved			
Engineer:	Remarks:			
Submittal Date:				
Notes 1:				
Notes 2:				