Anvil® Ceiling Plates & Flanges





Material Specifications

Size Range

1/2" through 8"

Material

Cast iron

Finish

Plain

Zinc Plated

Service

Gives finished appearance where pipe enters ceiling.

Installation

Sizes $\frac{1}{2}$ " to 4" furnished with one machine screw; sizes 5" to 8", two machine screws.

Ordering

Specify pipe size, figure number, name and finish.

Dimensions (In) - Weight (Lbs)

| Pipe Size | Weight | D - Dia. | L | Pipe Size | Weight | D - Dia. | L |
|-----------|--------|----------|-----|-----------|--------|----------|------|
| In. | Lbs. | In. | ln. | ln. | Lbs. | In. | In. |
| 1/2 | 0.21 | 27/8 | 3/4 | 21/2 | 0.93 | 51/2 | 1 |
| 3/4 | 0.40 | 33/8 | | 3 | 1.10 | 61/8 | 11, |
| 1 | 0.41 | 35/8 | | 4 | 1.40 | 71/8 | 11/8 |
| 11/4 | 0.51 | 4 | 1 | 5 | 2.50 | 8 11/16 | |
| 11/2 | 0.55 | 41/4 | | 6 | 3.10 | 93/4 | 11/4 |
| 2 | 0.67 | 43/4 | | 8 | 3.30 | 113/4 | |



| PROJECT INFORMATION | APPROVAL STAMP | |
|---------------------|-------------------|--|
| Project: | Approved | |
| Address: | Approved as noted | |
| Contractor: | Not approved | |
| Engineer: | Remarks: | |
| Submittal Date: | | |
| Notes 1: | | |
| Notes 2: | | |