



## REDUCING TEES



**FIG. 6061**



**FIG. 6064**

### DIMENSIONS/WEIGHTS – REDUCING TEES

Nominal Size	Fig. 6061 Groove x Groove x Groove			Fig. 6064 Groove x Groove x Cup			
	C to E	C to ØE	Wt. Ea	C to E	C to ØE	Cup Length	Wt Ea.
	In./mm	In./mm	Lbs./kg	In./mm	In./mm	In./mm	Lbs./kg
2 x 2 x ¾	—	—	—	2.20 56	1.98 50	0.75 19	0.88 0.40
2 x 2 x 1	—	—	—	2.33 59	2.20 56	0.91 23	1.03 0.47
2 x 2 x 1¼	—	—	—	2.48 63	2.35 60	0.97 25	1.12 0.51
2 x 2 x 1½	—	—	—	2.55 65	2.28 58	1.09 28	1.25 0.57
2½ x 2½ x ¾	—	—	—	2.27 58	2.18 55	0.75 19	1.25 0.57
2½ x 2½ x 1	—	—	—	2.40 61	2.40 61	0.91 23	1.38 0.63
2½ x 2½ x 1¼	—	—	—	2.52 64	2.57 65	0.97 25	1.56 0.71
2½ x 2½ x 1½	—	—	—	2.70 69	2.68 68	1.09 28	1.88 0.85
2½ x 2½ x 2	3.28 83	3.38 86	2.54 1.15	—	—	—	—
3 x 3 x ¾	—	—	—	2.45 62	2.60 66	0.75 19	1.88 0.85
3 x 3 x 1	—	—	—	2.54 65	2.79 71	0.91 23	2.04 0.93
3 x 3 x 1¼	—	—	—	2.63 67	2.89 73	0.97 25	2.13 0.97
3 x 3 x 1½	—	—	—	2.85 72	3.00 76	1.09 28	2.25 1.02
3 x 3 x 2	3.00 76	3.38 86	2.90 1.32	—	—	—	—
3 x 3 x 2½	3.25 83	3.50 89	3.16 1.43	—	—	—	—
4 x 4 x ¾	—	—	—	2.95 75	3.00 76	0.75 19	3.63 1.65
4 x 4 x 1	—	—	—	3.10 79	3.22 82	0.91 23	3.94 1.79
4 x 4 x 1¼	—	—	—	3.25 83	3.47 88	0.97 25	4.24 1.92
4 x 4 x 1½	—	—	—	3.35 85	3.65 93	1.09 28	4.47 2.03
4 x 4 x 2	3.66 93	4.13 105	5.14 2.33	—	—	—	—
4 x 4 x 2½	3.94 100	4.06 103	5.36 2.43	—	—	—	—
4 x 4 x 3	4.19 106	4.16 106	5.88 2.67	—	—	—	—
5 x 5 x 3	3.75 95	4.63 118	7.45 3.38	—	—	—	—
5 x 5 x 4	4.25 108	4.56 116	8.13 3.69	—	—	—	—
6 x 6 x 2½	3.63 92	5.13 130	9.42 4.27	—	—	—	—
6 x 6 x 3	3.69 94	5.19 132	10.06 4.56	—	—	—	—
6 x 6 x 4	4.19 106	5.13 130	10.86 4.93	—	—	—	—
6 x 6 x 5	4.69 119	5.19 132	12.73 5.77	—	—	—	—

#### PROJECT INFORMATION

#### APPROVAL STAMP

Project:	<input type="checkbox"/> Approved
Address:	<input type="checkbox"/> Approved as noted
Contractor:	<input type="checkbox"/> Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	