


Square Washer with Channel Guide Figs. AS 2504, AS 619, AS 601, AS 602, AS 620, AS 888




Description

Anvil–Strut Flat Plates are designed to fit with all Anvil–Strut $1^{5}/_{8}$ " wide channels. Unless otherwise noted, Anvil–Strut Miscellaneous Fittings are manufactured from 1^{4} " thick carbon steel, $1^{5}/_{8}$ " wide, all holes are $9'_{16}$ " diameter, spaced $1^{7}/_{8}$ " on center and $1^{3}/_{16}$ " from the end.

Square Washer

AS 619 EG, GR, SS, ZTC Bolt Size "A" 15/8"

Square Washer with Channel Guide



| Α | Wt./100 Pcs. | Rod Size | Hole Size | Wt./100 Pcs. |
|------------------|--------------|--|--------------------------------|--------------|
| 1/4" | 18 | 1/4" | ⁵ / ₁₆ " | 18 |
| 3/8" | 18 | 3/8" | ⁷ / ₁₆ " | 18 |
| 1/2" | 17 | 1/2" | ^{9/} 16" | 17 |
| ⁵ /8" | 16 | Std Pkg 100 – Wt/100 pcs: See chart above. | | |
| 3/4" | 15 | | p | |

Std Pkg 100 - Wt/100 pcs: See chart above.

7/8"

Page notes unless otherwise specified: ¼" thick, 15/6" wide, holes 3/16" diameter, spaced 17/6" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum
HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium.
Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes.
Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

14





| APPROVAL STAMP | |
|-------------------|--|
| Approved | |
| Approved as noted | |
| Not approved | |
| Remarks: | |
| _ | |
| | |
| | |
| | |



Square Washer with Channel Guide Figs. AS 2504, AS 619, AS 601, AS 602, AS 620, AS 888








Std Pkg 50 - Wt/100 pcs: 37 Lbs.


2-Hole Connecting Plate

AS 620 EG, GR



Std Pkg 50 - Wt/100 pcs: 34 Lbs.

3-Hole Splice Plate



Std Pkg 25 - Wt/100 pcs: 57 Lbs.

4-Hole Splice Plate AS 888 EG, GR, ZTC

Std Pkg 25 - Wt/100 pcs: 76 Lbs.

LEGEND:

GR: Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum **HG:** Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel **ZTC:** Zinc Trivalent Chromium. Stainless Steel **(SS)**, Zinc Trivalent Chromium (**ZTC)** and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

