


Single Column Post Base Figs. AS 3013, AS 3013SQ, AS 3033, AS 3033SQ




Description

Anvil-Strut Post Bases are designed to fit Anvil-Strut 15/8" wide channels. Anvil-Strut Post Bases are used to securely fasten channels to a surface.

Single Post Base


AS 3013 EG, GR



Use with AS 200 & AS 210 Std Pkg 10 - Wt/100 pcs: 307 Lbs.

Single Post Base

AS 3013SQ EG, GR



Use with AS 200 & AS 210 Std Pkg 5 - Wt/100 pcs: 314 Lbs.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes. $Pricing \ is \ located \ in \ the \ Special ty \ Strut \ Section \ of \ the \ Anvil-Strut \ price \ book.$




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	



Single Column Post Base Figs. AS 3013, AS 3013SQ, AS 3033, AS 3033SQ

Single Post Base


AS 3033 EG, GR, ZTC



Use with AS 200 & AS 210 Std Pkg 10 - Wt/100 pcs: 373 Lbs.

Single Post Base

AS 3033SQ EG, GR, ZTC



Use with AS 200 & AS 210 Std Pkg 10 - Wt/100 pcs: 392 Lbs.

LEGEND:

GR: Powder Coated Supr-Green **EG**: Electro-Galvanized **PG**: Pre-Galvanized **AL**: Aluminum **HG**: Hot Dipped Galvanized **PL**: Plain **SS**: Stainless Steel **ZTC**: Zinc Trivalent Chromium. Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

