



Three Hole Corner Angle Figs. AS 745, AS 921, AS 603, AS 604, AS 806, AS 606



Description

Anvil–Strut Angle Fittings and Connectors are designed to fit with all Anvil–Strut $1^{5}/_{8}$ " wide channels. Unless otherwise noted, Anvil–Strut Angle Fittings and Connectors are manufactured from $1/_{4}$ " thick carbon steel, $1^{5}/_{8}$ " wide, all holes are $9/_{16}$ " diameter, spaced $1^{7}/_{8}$ " on center and $1^{3}/_{16}$ " from the end.

1-Hole Angle



Catalog No.	А	Wt./100 Pcs.
AS 921 A	3 7⁄8"	61
AS 921 B	5 1/8"	84
AS 921 C	7 1/8"	107
AS 921 D	9 7⁄8"	130

Std Pkg 25 - Wt/100 pcs: See chart above.

Page notes unless otherwise specified: 1/4" thick, 15/8" wide, holes 9/16" diameter, spaced 17/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum
HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium
Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes.
Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	




Three Hole Corner Angle Figs. AS 745, AS 921, AS 603, AS 604, AS 806, AS 606

2-Hole End Angle




Std Pkg 50 - Wt/100 pcs: 37 Lbs.

2-Hole Corner Angle



Std Pkg 50 - Wt/100 pcs: 37 Lbs.

2-Hole Angle With Impressions on Both Legs



Std Pkg 50 - Wt/100 pcs: 39 Lbs.

3-Hole Corner Angle AS 745 EG, GR, ZTC


Std Pkg 25 - Wt/100 pcs: 57 Lbs.





Three Hole Corner Angle Figs. AS 745, AS 921, AS 603, AS 604, AS 806, AS 606

3-Hole Corner Angle



Std Pkg 50 - Wt/100 pcs: 57 Lbs.

Page notes unless otherwise specified: 1/4" thick, 15/8" wide, holes 9/16" diameter, spaced 17/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum
HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium
Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes.
Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

