


Four Hole Open Angle Connector

Fig. AS 781, AS 633, AS 624




Description

Anvil–Strut Angle Fittings and Connectors are designed to fit with all Anvil–Strut $1^5/8^{"}$ wide channels. Unless otherwise noted, Anvil–Strut Angle Fittings and Connectors are manufactured from $1/4^{"}$ thick carbon steel, $1^5/8^{"}$ wide, all holes are $9/16^{"}$ diameter, spaced $1^7/8^{"}$ on center and $1^3/16^{"}$ from the end.

2-Hole Open Angle Connector

AS 633 EG, GR, ZTO



Α	В	С	Wt./100 Pcs.
82½°	31/2"	21/8"	63
75°	31/2"	21/8"	63
67½°	31/2"	21/8"	63
60°	31/2"	21/8"	63
52½°	31/2"	21/8"	63
45°	3"	21/8"	60
37½°	31/2"	21/8"	63
30°	35/16"	21/16"	59
22½°	35/16"	21/16"	59
15°	35/16"	21/16"	59
7½°	35/16"	21/16"	59

Std Pkg 25 - Wt/100 pcs: See chart above.

Page notes unless otherwise specified: $^{1}/_{4}$ " thick, $^{1}5/_{8}$ " wide, holes $^{9}/_{16}$ " diameter, spaced $^{17}/_{8}$ " on center and $^{13}/_{16}$ " from end.

LEGEND:

GR: Powder Coated Supr-Green **EG**: Electro-Galvanized **PG**: Pre-Galvanized **AL**: Aluminum **HG**: Hot Dipped Galvanized **PL**: Plain **SS**: Stainless Steel

ZTC: Zinc Trivalent Chromium Stainless Steel (SS), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil–Strut price book.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	



Four Hole Open Angle Connector Fig. AS 781, AS 633, AS 624

2-Hole Closed Angle Connector

AS 624 EG, GR, ZTC


А
37½°
45°
52½°
60°
67½°
75°
82½°

Std Pkg 25 - Wt/100 pcs: 63 Lbs.

4-Hole Open Angle Connector

AS 781

EG, C



Std Pkg 25 - Wt/100 pcs: 78 Lbs.

А
71/2°
15°
22½°
30°
37½°
45°
52½°
60°
67½°
75°
82½°

Page notes unless otherwise specified: $^{1}/_{4}$ " thick, 1 $^{5}/_{8}$ " wide, holes $^{9}/_{16}$ " diameter, spaced 1 $^{7}/_{8}$ " on center and $^{13}/_{16}$ " from end.

LEGEND:

GR: Powder Coated Supr-Green **EG**: Electro-Galvanized **PG**: Pre-Galvanized **AL**: Aluminum **HG**: Hot Dipped Galvanized **PL**: Plain **SS**: Stainless Steel

ZTC: Zinc Trivalent Chromium Stainless Steel (SS), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil–Strut price book.

