



45° Stair Tread Support Figs. AS 2421, AS 2422, AS 926, AS 993, AS 825




Description

Anvil–Strut Miscellaneous Fittings are designed to fit with all Anvil–Strut $1^{5}/_{8}$ " wide channels. Unless otherwise noted, Anvil–Strut Miscellaneous Fittings are manufactured from 1^{4} " thick carbon steel, $1^{5}/_{8}$ " wide, all holes are $9'_{16}$ " diameter, spaced $1^{7}/_{8}$ " on center and $1^{3}/_{6}$ " from the end.



Inside Clevis



| А | В | Std. Pkg. | Wt./100 Pcs. | Α | Std. Pkg. | Wt./100 Pcs. |
|-----------|-------------|----------------|--------------|----|-----------|--------------|
| 24" | - | Bulk | 280 | 4" | 25 | 89 |
| 165⁄8" | 135⁄8" | 10 | 232 | 5" | 25 | 93 |
| 12" | 101/8" | 15 | 175 | 6" | 25 | 106 |
| Std Pkg & | Wt/100 pcs: | See chart abov | e | 7" | 25 | 118 |
| Ū | · | | | 8" | 20 | 132 |

Std Pkg & Wt/100 pcs: See chart above.

Page notes unless otherwise specified: ¼" thick, 15/8" wide, holes 3/16" diameter, spaced 17/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum
HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel ZTC: Zinc Trivalent Chromium.
Stainless Steel (SS), Zinc Trivalent Chromium (ZTC) and Hot Dipped Galvanized (HG) are specialty finishes.
Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.




| PROJECT INFORMATION | APPROVAL STAMP |
|---------------------|-------------------|
| Project: | Approved |
| Address: | Approved as noted |
| Contractor: | Not approved |
| Engineer: | Remarks: |
| Submittal Date: | |
| Notes 1: | |
| Notes 2: | |
| | |



45° Stair Tread Support Figs. AS 2421, AS 2422, AS 926, AS 993, AS 825

RH & LH Pipe Axle Support




| Catalog No. | А | Wt./100 Pcs. | |
|-------------|-------|--------------|--|
| AS 825LH | 35⁄8" | 220 | |
| AS 825RH | 35⁄8" | 220 | |

Std Pkg & Wt/100 pcs: See chart above.

45° Stair Support


AS 2421 GR, HG



Std Pkg 20 - Wt/100 pcs: 220 Lbs.

371/2° Stair Support

AS 2422 GR, HG



Std Pkg 25 - Wt/100 pcs: 206 Lbs.

LEGEND:

GR: Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum **HG:** Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel **ZTC:** Zinc Trivalent Chromium. Stainless Steel **(SS)**, Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.

