

Universal Open Hub Fig. BKT-UHO3



Fig. BKT-UHO3 FM	Approved Hoses
Hose Figure #	FM Approved
20XXT	✓
20XXET	\checkmark
20XXE	\checkmark
20XXSF	✓
20XXSF-CS	✓
20XXSF-SLT	\checkmark
20XXSF-CS-SLT	✓
20XXH	✓
20XXHE	✓
20XXI	✓
20XX-DPS	\checkmark
20XX-DPS-DT	\checkmark

Note: Brackets are only FM Approved when installed with FlexHead brackets listed above.

Product Specifications

Material

Carbon Steel – Galvanized

Applications

- Freezers & Insulated Metal Panels
- Institutional ³/₈" Threaded Rod 4ft Length
- 1⁄2" Threaded Rod 6ft Length
- Temporary Fire Protection

Features

- Open hub design for ease of installation
- Direct connection to structure

• Ordering

Specify figure number & description



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	


FLEXHEAD® Flexible Sprinkler Hose Solutions



Universal Open Hub Fig. BKT-UHO3


Applications






Installation with two (2) FAB-LOK Fastners (FAB-LOK Fasteners Sold Separately)

Threaded Rod



Applications with ³/₈" & ¹/₂" Threaded Rod (Threaded Rod Sold Separately) Institutional - Ceiling or Sidewall



Shown with 20XXI - Institutional Hose





Universal Open Hub Fig. BKT-UHO3




Fig. BKT-UHO3 Dimensions & Model Number

L	W	н	Α	FlexHead Historical Model Number
In/mm	ln/mm	in/mm	in/mm	Model Number
4.09 103.9	2.28 57.9	1.14 29.0	3.30 83.8	UHO-3

Installation Instructions

Connection to the Flexible Sprinkler Hose

- 1 Open the hinge door on the bracket hub by rotating the locking shaft ¼ turn.
- 2 Slide the flexible hose drop into the hub.
- $\frac{3}{2}$ Close the hinge door and re-lock the locking shaft with a $\frac{1}{4}$ turn.
- 4 Ensure the flexible hose drop is straight and not applying a substantial moment on the bracket which may cause sprinkler misalignment.
- 5 Adjust the flexible hose drop to the desired height and tighten the set screw hand-tight plus a ³/₄ turn (130 in-lbs).

Connection to Freezers and Insulated Metal Panels

- 1 Position the center of the hub over the sprinkler hole and ensure the sprinkler is in the desired position.
- 2 Install fasteners into the mounting holes. Fastener options listed below.
 - a Two (2) FAB-LOK EZJ 120 5/16" x 1.612 Fasteners (sold separately)
 - b Two (2) 1/4" or 5/16" Approved Fasteners

Institutional, Sidewall, & Ceiling Installation

- 1 Position the center of the hub over the sprinkler hole and ensure the sprinkler is in the desired position.
- 2 Install fasteners into the mounting holes. Fastener options listed below.
 - **a** Two (2) FAB-LOK EZJ120 5/16x1.612 Fasteners (sold separately)
 - b Two (2) 1/4" or 5/16" Approved Fasteners

Connection to Threaded Rod

- 1 Insert the threaded rod (not included) into the $\frac{3}{8}$ or $\frac{1}{2}$ mounting hole.
- 2 Move the bracket to the correct elevation.
- $\frac{3}{100}$ Tighten the set screw hand tight plus a $\frac{3}{4}$ (130 in-lbs).
- 4 Note: The set screw may be moved between the 3/8" and 1/2" threaded rod mounting hole.

General Notes

Installation & maintenance of FlexHead products shall be in accordance with applicable local and federal codes (E.g. NFPA 13, NFPA 13R, NFPA 13D, NFPA 25, FM Datasheets, IBC).

