SPF/Anvil® Grooved Fittings





Material Specifications

Fabricated Fittings

1"-10" Carbon Steel, Schedule 40, conforming to ASTM A53, Grade B **12"** Carbon Steel, Standard Wall, conforming to ASTM A53, Grade B

Coatings

Rust inhibiting paint
Color: Orange (standard)
Hot Dipped Zinc Galvanized
conforming to ASTM A153 (optional)
Other available options
Example: RAL3000 or RAL9000 Series

For Listings/Approval Details and Limitations, visit our website at www.asc−es.com or contact an ASC Engineered Solutions™ Sales Representative.




PROJECT INFORMATION	APPROVAL STAMP	
Project:	Approved	
Address:	Approved as noted	
Contractor:	Not approved	
Engineer:	Remarks:	
Submittal Date:		
Notes 1:		
Notes 2:		

SPF/Anvil® Grooved Fittings



111/4° Elbow **Fig. E-4**



Nominal Size	O.D.	Max. Working Pressure	Center to End	Approx. Wt. Ea.
In./DN(mm)	In./mm	PSI/bar	In./mm	Lbs./kg
11/4	1.660	300	13/8	0.5
32	42.2	20.7	35	0.2
11/2	1.900	300	13/8	0.7
40	48.3	20.7	35	0.3
2	2.375	300	13/8	0.9
50	60.3	20.7	35	0.4
21/2	2.875	300	1½	1.5
65	73.0	20.7	38	0.7
3	3.500	300	1½	2.0
80	88.9	20.7	38	0.9
4	4.500	300	13/4	3.3
100	114.3	20.7	44	1.5
5	5.563	300	2	5.0
125	141.3	20.7	51	2.3
6	6.625	300	2	6.5
150	168.3	20.7	51	2.9
8	8.625	300	2	10.0
200	219.1	20.7	51	4.5
10	10.750	300	21/8	14.5
250	273.1	20.7	54	6.6
12	12.750	300	21/4	29.3
300	323.9	20.7	57	13.3



asc-es.com

Building connections that last™