

Breakable Caps, Plastic

Description

The Plastic Breakable Caps for Fire department Connections are injection molded polystyrene. Each set includes two caps and 4 eyelets with nuts for 2½” swivels. The caps have been molded with “scored” tabs for easy removal with a hydrant wrench or other similar tool. Plastic Breakable caps provide protection against the introduction of foreign material into the swivels but allow for quick access when a hose connection is necessary.



Installation

Remove the caps from their packaging. Hold the breakable cap to the opening of swivel. Align the breakable tabs with the pin lugs on the swivel. Once aligned, insert the threaded end of one eyelet through the hole in the tab of the cap then slide the eyelet over the pin lug. Once the eyelet is in place, carefully thread the included ¼-20 finished hexnut on to the threaded end of the eyelet until snug.

Caution: Do not overtighten. The tabs of the break caps are designed to break with minimal force.

Specifications


Material:
Injection Molded Polystyrene

Size:
2½” swivel

Type:
Pin lug

Included per set:
(2) caps
(4) eyelets
(4) finished hexnuts

Available in sets only



3198 LIONSHEAD AVE
CARLSBAD, CA 92010
TEL + 1 760 599-1168
+ 1 800 344-1822
FAX + 1 800 344-3775

© 2012 Fire Protection Products, Inc.