

Drain Cap
Fig. K-9



Material Specifications

Cast Fittings

Ductile Iron conforming to ASTM A536

Coatings

Rust inhibiting paint

Color: Orange (standard)

Hot Dipped Zinc Galvanized conforming to ASTM A153 (optional)

Other available options

Example: RAL3000 or RAL9000 Series

For Listings/Approval Details and Limitations, visit our website at www.asc-es.com or contact an ASC Engineered Solutions™ Sales Representative.



| PROJECT INFORMATION | APPROVAL STAMP |
|---------------------|-------------------|
| Project: | Approved |
| Address: | Approved as noted |
| Contractor: | Not approved |
| Engineer: | Remarks: |
| Submittal Date: | |
| Notes 1: | |
| Notes 2: | |

Drain Cap Fig. K-9

| Nominal Size | O.D. | End to End | Approx. Wt. Ea. | Nominal Size | O.D. | End to End | Approx. Wt. Ea. |
|--------------|--------|------------|-----------------|--------------|--------|------------|-----------------|
| In./DN(mm) | In./mm | In./mm | Lbs./kg | In./DN(mm) | In./mm | In./mm | Lbs./kg |
| 1¼ | 1.660 | — | 0.71 | 4 | 4.500 | — | 2.92 |
| 32 | 42.2 | — | 0.30 | 100 | 114.3 | — | 1.32 |
| 1½ | 1.900 | — | 0.76 | 5 | 5.563 | — | 3.40 |
| 40 | 48.3 | — | 0.30 | 125 | 141.3 | — | 1.50 |
| 2 | 2.375 | — | 0.83 | 6 | 6.625 | — | 4.02 |
| 50 | 60.3 | — | 0.38 | 150 | 168.3 | — | 1.82 |
| 2½ | 2.875 | — | 1.06 | 8 | 8.625 | — | 6.66 |
| 65 | 73.0 | — | 0.48 | 200 | 219.1 | — | 3.02 |
| 3 | 3.500 | — | 1.27 | | | | |
| 80 | 88.9 | — | 0.58 | | | | |

Note:

K-9 is also available in ¾" and ½" at same list price as 1" pol.



asc-es.com

Building connections that last™