


Light Duty Stainless Steel Band Hanger **Fig. 69SSG**



Size Range: ½" through 8" NPS

Material: 316 Stainless Steel

Service: Recommended for the suspension of stationary steel pipe.

Maximum Temperature: 650° F

Approvals: MSS SP-58 (Type-10)

Installation: Supplied with two stainless steel hex nuts.

Ordering: Nominal pipe size, rod diameter,

figure number and name.

Notes:

 For U.S. domestic product contact ASC Engineered Solutions[™] for a quote.



Fig. 69SSG: Dimensions (in) •	Loads (lbs) • Rod Siz	e (in)
-------------------------------	------------	-------------	--------

Pipe Size	Max load	Steel Size	Rod Size A	NFPA Rod Size A	В	С	Rod Take-Out E	Adjustment F
1/2	610	16GA X 1	3/8	3/8	113/16	215/16	11//8	1
3/4	610	16GA X 1	3/8	3/8	21/16	25/8	15/16	1
1	610	16GA X 1	3/8	3/8	23/16	27/8	17/16	1
11//4	610	16GA X 1	3/8	3/8	29/16	37/16	113/16	11/4
11//2	610	16GA X 1	3/8	3/8	23/4	311/16	115/16	11/4
2	610	¹/ ₈ X 1	3/8	3/8	3	43/16	23/16	11//4
21/2	970	¹/ ₈ X 1	1/2	3/8	37/8	55/16	3	13/4
3	970	¹/ ₈ X 1	1/2	3/8	41/4	6	35/16	13/4
31/2	970	¹/ ₈ X 1	1/2	3/8	41/2	61/2	39/16	13/4
4	1250	1/8 X 11/4	5/8	3/8	47/8	71/8	313/16	13/4
5	1250	1/8 X 11/4	5/8	1/2	511/16	87/16	45/8	2
6	1600	1/8 X 11/2	3/4	1/2	63/8	911/16	53/16	2
8	1800	3/ ₁₆ X 1 ¹ / ₂	7/8	1/2	79/16	117/8	63/16	2

PROJECT INFORMATION	APPROVAL STAMP	
Project:	Approved	
Address:	Approved as noted	
Contractor:	Not approved	
Engineer:	Remarks:	
Submittal Date:		
Notes 1:		
Notes 2:		