

Plastic Wall Plates Floor/Ceiling Fig. 01-232



Specifications

Size(IP)*	ID	OD
1/2"	.827	2.787
3/4"	1.037	2.997
1"	1.298	3.210
1 1/4"	1.640	3.580
1 1/2"	1.900	3.900
2"	2.380	4.450
2 1/2"	2.900	5.280
3"	3.535	5.925
4"	4.575	6.935
5"	5.655	9.655
6"	6.740	9.820
8"	8.790	13.010

Depth:
3/16"

Finish:
Chrome
White

Description

FPPI Plastic Floor and Ceiling Plates are manufactured from light weight injection molded plastic and are of single piece construction and rustproof. They are suitable for both interior and exterior uses and are highly recommended in corrosive environments. Available in IP sizes 1/2" through 8".

Installation

The plastic wall plates may be installed by two methods. The first is by placing the wall plate over the pipe while the pipe is being installed. The second is by splitting the wall plate at the area on the back of the wall plates that has been molded to break apart. Carefully bend the wall plate at this weakened area until fully separated. Then carefully twist the wall plate open just enough to be placed around the pipe. Allow the two ends of the separated wall plate to "spring" back into shape. Slide the wall plate up against the base material to finish the installation. The wall plates should not be painted. Certain chemicals contained in paint may cause the wall plates to deteriorate.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	