



DIMENSION	2"	2-1/2"	3"	4"	5"	6"	8"	10"	12"
A (SR)	12.4	14.1	14.9	17.6	19.1	20.0	26.2	others	others
A (DA)	11.7	12.5	14.0	16.7	17.1	19.0	23.3	27.2	35.4*
B (SR)	8.1	9.9	9.9	14.0	16.7	16.7	25.3	others	others
B (DA)	5.7	5.7	5.9	7.2	7.2	10.3	12.0	14.4	19.3
C (SR)	6.5	7.6	8.0	9.6	10.0	10.5	13.7		
C (DA)	6.2	6.8	7.5	9.1	8.9	9.8	12.4	14.6	20.4*
D	3.3	3.6	3.9	4.6	5.1	5.6	7.0	8.1	9.6
F (SR)	1.7	2.1	2.1	2.5	2.7	2.7	3.8		
F (DA)	1.3	1.3	1.7	2.1	2.1	2.5	2.7	2.9	3.8
G (SR)	2.1	2.6	2.6	3.0	4.2	4.2	5.0		
G (DA)	1.9	1.9	2.1	2.6	2.6	3.0	4.2	4.3	5.0
H (SR)	3.5	4.0	4.0	4.4	5.6	5.6	6.4		
H (DA)	3.3	3.3	3.5	4.0	4.0	4.4	5.6	5.7	6.4
J (SR)	3.4	4.2	4.2	5.0	5.4	5.4	7.6		
J (DA)	2.6	2.6	3.5	4.2	4.2	5.0	5.5	5.7	7.6
K	1.7	1.8	1.8	2.1	2.2	2.2	2.4	2.7	3.1

NOTE: "H" IS CENTERLINE TO OUTSIDE SURFACE OF SOLENOID-
ADD 1-1/8" IF EQUIPPED WITH QUADRANT BREATHER BLOCK

Note: 1. Asterisk indicates use of 4" square mounting bracket
2. All dimensions in inches

**2" thru 12" Series BFV-A with C-Series Pneumatic
Actuator 200PSID DRY SERVICE**

