



DIMENSION	2"	2-1/2"	3"	4"	5"	6"	8"	10"	12"
A (SR)	12.4	13.2	14.8	16.7	18.3	20.0	28.3*	33.1*	others
A (DA)	11.7	12.5	13.3	16.7	17.1	18.1	22.2	26.1	29.6
B (SR)	8.1	8.1	9.9	9.9	14.0	16.7	19.2	25.3	others
B (DA)	5.7	5.7	5.7	7.2	7.2	7.2	10.3	12.0	14.4
C (SR)	6.5	7.1	8.0	9.1	9.3	10.5	16.8*	19.5*	
C (DA)	6.2	6.8	7.2	9.1	8.9	9.4	11.7	14.2	15.5
D	3.3	3.6	3.9	4.6	5.1	5.6	7.0	8.1	9.6
F (SR)	1.7	1.7	2.1	2.1	2.5	2.7	2.9	3.8	
F (DA)	1.3	1.3	1.3	2.1	2.1	2.1	2.5	2.7	2.9
G (SR)	2.1	2.1	2.6	2.6	3.0	4.2	4.3	5.0	
G (DA)	1.9	1.9	1.9	2.6	2.6	2.6	3.0	4.2	4.3
H (SR)	3.5	3.5	4.0	4.0	4.4	5.6	5.7	6.4	
H (DA)	3.3	3.3	3.3	4.0	4.0	4.0	4.4	5.6	5.7
J (SR)	3.4	3.4	4.2	4.2	5.0	5.4	5.8	7.6	
J (DA)	2.6	2.6	2.6	4.2	4.2	4.2	5.0	5.4	5.8
K	1.7	1.8	1.8	2.1	2.2	2.2	2.4	2.7	3.1

NOTE: "H" IS CENTERLINE TO OUTSIDE SURFACE OF SOLENOID-  
ADD 1-1/8" IF EQUIPPED WITH QUADRANT BREATHER BLOCK

Note: 1. Asterisk indicates use of 4" square mounting bracket  
2. All dimensions in inches.

**2" thru 12" Series BFV-A with C-Series Pneumatic Actuator  
200PSID WET SERVICE**

