

Variable Spring

Check List for Requesting a Quote or Ordering

Page ___ of ___

Finish: Standard Primer: _____ Galvanized: _____ Special Coating: _____

Quantity: _____

Figure No.: Options are: 82, B-268, 98, Triple, Quadruple
or: C-82, C-268, C-98, Triple-CR, Quadruple-CR

Size: Options are: #0 through #22 (B-268 / C-268 also available in #00 and #000) _____

Type: Options are: A through G* _____

Hot (Operating or Design) Load (lbs): _____ (optional) **

Cold/Installed (Factory Set) Load (lbs): _____ (optional) **

Vertical Movement: _____ + (up) or - (down) (optional) **

Mark Number: _____ (If Required)

Travel Stops: Yes: _____ No: _____

If travel stops are ordered and hot & cold loads are not provided, then the spring will be set to mid range load.

Lifting Lugs: Yes: _____ No: _____

Available on sizes weighing 100 lbs or more.

Notes:

* Type G Springs must also include the C-to-C dimension & the load per spring.

** Anvil will determine the appropriate Figure Number and will calculate the Cold Load when only the Hot Load and movement are specified.

For technical information regarding Variable Springs contact:
Phone Number: (401) 886-3020 Email: eps_contact@anvilintl.com

ASC Engineered Solutions

Power & Process Division

160 Frenchtown Road, North Kingstown, RI 02852

T 401-886-3000 F 401-886-3010

www.asc-es.com