

WARDFlex® Tubing & Components Pietro Regulators



Pietro regulators are appliance regulators used to control and adjust pressures for 2.0 PSI and 10.0 PSI systems.

Features

- Suitable for a variety of gases including natural gas and LPG
- Comes with both an internal vent limiter and an external vent limiter
- Outlet pressures can be adjusted from 6" W.C. to 14" W.C.
- Outlet Pressures preset at 8" (Natural Gas) or 11" (Liquid Propane Gas)

Listings

- CSA 6.22a/ANSI Z21.80

Technical Data

For more information visit

www.fiorentini.com/us/en/product/components/gasinside



Regulator Capacities

WARDFlex Item #	Pietro Item #	Size	Inlet Pressure	Outlet Pressure	Capacity at 14" W.C. Inlet (BTU/HR)*	Capacity at 1.0 PSIG Inlet (BTU/HR)*	Capacity at 2.0 PSIG Inlet (BTU/HR)*
730	31051	1/2"	2.0 PSIG	8" W.C.	386,000	522,000	785,000
731	31051	1/2"	2.0 PSIG	11" W.C.	218,000	511,000	785,000
732	31052	3/4"	2.0 PSIG	8" W.C.	369,000	655,000	946,000
736	31052	3/4"	2.0 PSIG	11" W.C.	363,000	616,000	946,000
737	31053	1 1/4"	2.0 PSIG	8" W.C.	2,071,000	3,735,000	5,311,000

WARDFlex Item #	Pietro Item #	Size	Inlet Pressure	Outlet Pressure	Capacity at 3.0 PSIG Inlet (BTU/HR)*	Capacity at 5.0 PSIG Inlet (BTU/HR)*	Capacity at 10.0 PSIG Inlet (BTU/HR)*
735	31051OPD	1/2"	10.0 PSIG	8" W.C.	785,000	785,000	785,000
731	31052OPD	3/4"	10.0 PSIG	8" W.C.	946,000	946,000	946,000
732	31053OPD	1 1/4"	10.0 PSIG	8" W.C.	5,311,000	5,311,000	5,311,000

*Based on a specific gravity of 0.60

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	