

Hanger Size No.	Total Travel* (IN); Load (LBS)														
	1½	2	2½	3	3½	4	4½	5	5½	6	6½	7	7½	8	8½
1	144	108	86	72	62	54	48	43	39	36	33	31	29	27	
	173	130	104	87	74	65	58	52	47	43	40	37	35	33	
2	204	153	122	102	87	77	68	61	56	51	47	44	41	38	
3	233	175	140	117	100	88	78	70	64	58	54	50	47	44	
4	280	210	168	140	120	105	93	84	76	70	65	60	56	53	
5	327	245	196	163	140	123	109	98	89	82	75	70	65	61	
6	373	280	224	187	160	140	124	112	102	93	86	80	75	70	
7	451	338	270	225	193	169	150	135	123	113	104	97	90	85	
8	527	395	316	263	226	198	176	158	144	132	122	113	105	99	
9	600	450	360	300	257	225	200	180	164	150	138	129	120	113	
10	727	545	436	363	311	273	242	218	198	182	168	156	145	136	
11	851	638	510	425	365	319	284	255	232	213	196	182	170	160	
12	977	733	586	489	419	367	326	293	267	244	226	209	195	183	
13	1,177	883	706	589	505	442	392	353	321	294	272	252	235	221	
14	1,373	1,030	824	687	589	515	458	412	375	343	317	294	275	258	
15	1,573	1,180	944	787	674	590	524	472	429	393	363	337	315	295	
16	1,893	1,420	1,136	947	811	710	631	568	516	473	437	406	379	355	
17	2,217	1,663	1,330	1,109	950	832	739	665	605	554	512	475	443	416	
18	2,540	1,905	1,524	1,270	1,089	953	847	762	693	635	586	544	508	476	
19		2,025	1,620	1,350	1,157	1,013	900	810	736	675	623	579	540	506	448
															476
20		2,145	1,716	1,430	1,226	1,073	953	858	780	715	660	613	572	536	505
21		2,335	1,868	1,557	1,334	1,168	1,038	934	849	778	718	667	623	584	549
22		2,525	2,020	1,683	1,443	1,263	1,122	1,010	918	842	777	721	673	631	594
23		2,710	2,168	1,807	1,549	1,355	1,204	1,080	985	903	834	775	723	678	638
24		2,910	2,328	1,940	1,663	1,455	1,293	1,164	1,058	970	895	831	776	728	685
25		3,110	2,488	2,073	1,777	1,555	1,382	1,244	1,131	1,037	957	889	829	778	732
26		3,310	2,648	2,207	1,891	1,655	1,471	1,324	1,204	1,103	1,018	946	883	828	779
27		3,630	2,904	2,420	2,074	1,815	1,613	1,452	1,320	1,210	1,117	1,037	968	908	854
28		3,950	3,160	2,633	2,257	1,975	1,756	1,580	1,436	1,317	1,215	1,129	1,053	988	929
29		4,270	3,416	2,847	2,440	2,135	1,898	1,708	1,553	1,423	1,314	1,220	1,139	1,068	1,005
30		4,535	3,628	3,023	2,591	2,268	2,016	1,814	1,649	1,512	1,395	1,296	1,209	1,134	1,067
31		4,795	3,836	3,197	2,740	2,398	2,131	1,918	1,744	1,598	1,475	1,370	1,279	1,199	1,128
32		5,060	4,048	3,373	2,891	2,530	2,249	2,024	1,840	1,687	1,557	1,446	1,349	1,265	1,191
"B" (avg. in.)	1¾	1¾	2¼	2¼	3¼	3¾	4¾	4¾	5¾	5½	6	6½	6¾	7¾	7¾

Table continues of following page.

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com



asc-es.com

Building connections that last™

Hanger Size No.	Total Travel* (IN); Load (LBS)														
	1½	2	2½	3	3½	4	4½	5	5½	6	6½	7	7½	8	8½
33		5,295	4,236	3,530	3,026	2,648	2,353	2,118	1,925	1,765	1,629	1,513	1,412	1,324	1,246
34		5,525	4,420	3,683	3,157	2,763	2,456	2,210	2,009	1,842	1,700	1,579	1,473	1,381	1,300
35			4,696	3,913	3,354	2,935	2,609	2,348	2,135	1,957	1,806	1,677	1,565	1,468	1,381
36			4,968	4,140	3,549	3,105	2,760	2,484	2,258	2,070	1,911	1,774	1,656	1,553	1,461
37			5,240	4,367	3,743	3,275	2,911	2,620	2,382	2,183	2,015	1,871	1,747	1,638	1,541
38			5,616	4,680	4,011	3,510	3,120	2,808	2,553	2,340	2,160	2,006	1,872	1,755	1,652
39			5,988	4,990	4,277	3,743	3,327	2,994	2,722	2,495	2,303	2,139	1,996	1,871	1,761
40			6,360	5,300	4,543	3,975	3,533	3,180	2,891	2,650	2,446	2,271	2,120	1,988	1,871
41			6,976	5,813	4,983	4,360	3,876	3,488	3,171	2,907	2,683	2,491	2,325	2,180	2,052
42			7,588	6,323	5,420	4,743	4,216	3,794	3,449	3,162	2,919	2,710	2,529	2,371	2,232
43			8,200	6,833	5,857	5,125	4,556	4,100	3,727	3,417	3,154	2,929	2,733	2,563	2,412
44			8,724	7,270	6,231	5,453	4,847	4,362	3,965	3,635	3,355	3,116	2,908	2,726	2,566
45			9,284	7,737	6,631	5,803	5,158	4,642	4,220	3,868	3,571	3,316	3,095	2,901	2,731
46			9,760	8,133	6,971	6,100	5,422	4,880	4,436	4,067	3,754	3,486	3,253	3,050	2,871
47			10,376	8,647	7,411	6,485	5,764	5,188	4,716	4,323	3,991	3,706	3,459	3,243	3,052
48			10,988	9,157	7,848	6,868	6,104	5,494	4,995	4,578	4,226	3,924	3,663	3,434	3,232
49			11,600	9,667	8,286	7,250	6,444	5,800	5,273	4,833	4,462	4,143	3,867	3,625	3,412
50				10,367	8,886	7,775	6,911	6,220	5,655	5,183	4,785	4,443	4,147	3,888	3,659
51				11,067	9,486	8,300	7,378	6,640	6,036	5,533	5,108	4,743	4,427	4,150	3,906
52				11,847	10,154	8,885	7,898	7,108	6,462	5,923	5,468	5,077	4,739	4,443	4,181
53				12,623	10,820	9,468	8,415	7,574	6,886	6,311	5,826	5,410	5,049	4,734	4,455
54				13,400	11,486	10,050	8,933	8,040	7,309	6,700	6,185	5,743	5,360	5,025	4,730
55				14,713	12,611	11,035	9,809	8,828	8,026	7,356	6,791	6,306	5,885	5,518	5,193
56				16,023	13,734	12,018	10,682	9,614	8,740	8,011	7,396	6,867	6,409	6,009	5,655
57				17,333	14,857	13,000	11,555	10,400	9,455	8,666	8,000	7,429	6,933	6,500	6,118
58				18,423	15,791	13,818	12,282	11,054	10,049	9,211	8,503	7,896	7,369	6,809	6,503
59				19,510	16,723	14,633	13,007	11,706	10,642	9,755	9,005	8,362	7,804	7,316	6,886
60				20,600	17,657	15,450	13,733	12,360	11,236	10,300	9,508	8,829	8,240	7,725	7,271
61				21,890	18,763	16,418	14,593	13,134	11,940	10,945	10,103	9,382	8,756	8,209	7,726
62				23,176	19,665	17,383	15,451	13,906	12,642	11,588	10,697	9,933	9,270	8,691	8,180
63				24,463	20,968	18,348	16,309	14,678	13,344	12,231	11,291	10,484	9,785	9,174	8,634
"B" (avg. in.)	1¾	1⅞	2¼	2½	3¼	3⅝	4⅞	4⅞	5⅞	5½	6	6½	6⅞	7⅞	7⅞

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com



asc-es.com

Building connections that last™

Hanger Size No.	Total Travel* (IN); Load (LBS)														
	9	9½	10	10½	11	11½	12	12½	13	13½	14	14½	15	15½	16
1															
2															
3															
4															
5															
6															
7															
8															
9															
10															
11															
12															
13															
14															
15															
16															
17															
18															
19	423	401	381												
20	450	426	405												
21	477	452	429												
22	519	492	467												
23	561	532	505												
24	602	571	542												
25	647	613	582												
26	691	655	622												
27	736	697	662												
28	807	764	726												
29	878	832	790												
30	949	899	854												
31	1,008	955	907												
32	1,066	1,009	959												
33	1,124	1,065	1,012												
34	1,177	1,115	1,059												
"B" (avg. in.)	8¼	8¾	9¼	9⅝	10⅞	10⅝	11	11½	12	12¾	12⅞	13¾	13⅞	14¼	14¾

Table continues on the following page.

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com



asc-es.com

Building connections that last™

Hanger Size No.	Total Travel* (IN); Load (LBS)															
	9	9½	10	10½	11	11½	12	12½	13	13½	14	14½	15	15½	16	
34	1,228	1,163	1,105													
35	1,304	1,236	1,174	1,053	1,005	962	922	885	851	819	790					
				1,118	1,067	1,021	978	939	903	870	838					
36	1,380	1,307	1,242	1,183	1,129	1,080	1,035	994	955	920	887					
37	1,456	1,379	1,310	1,248	1,191	1,139	1,092	1,048	1,008	970	936					
38	1,560	1,478	1,404	1,337	1,276	1,221	1,170	1,123	1,080	1,040	1,003					
39	1,663	1,576	1,497	1,426	1,361	1,302	1,247	1,198	1,151	1,109	1,069					
40	1,767	1,674	1,590	1,514	1,445	1,383	1,325	1,272	1,223	1,178	1,136					
41	1,938	1,836	1,744	1,661	1,585	1,516	1,453	1,395	1,341	1,292	1,246					
42	2,108	1,997	1,897	1,807	1,724	1,649	1,581	1,518	1,459	1,405	1,355					
43	2,278	2,158	2,050	1,952	1,863	1,782	1,708	1,640	1,577	1,518	1,464					
44	2,423	2,296	2,181	2,077	1,983	1,896	1,817	1,745	1,678	1,615	1,558					
45	2,579	2,443	2,321	2,210	2,110	2,018	1,934	1,857	1,785	1,719	1,658					
46	2,711	2,568	2,440	2,324	2,218	2,122	2,033	1,952	1,877	1,807	1,743					
47	2,882	2,730	2,594	2,470	2,358	2,255	2,162	2,075	1,995	1,921	1,853					
48	3,052	2,891	2,747	2,616	2,497	2,389	2,289	2,198	2,113	2,035	1,962					
49	3,222	3,053	2,900	2,762	2,636	2,522	2,417	2,320	2,231	2,148	2,071					
50	3,456	3,274	3,110	2,962	2,827	2,704	2,592	2,488	2,392	2,304	2,221	2,001	1,934	1,871	1,813	
												2,145	2,073	2,006	1,944	
51	3,689	3,495	3,320	3,162	3,018	2,887	2,767	2,656	2,554	2,459	2,371	2,289	2,213	2,142	2,075	
52	3,949	3,741	3,554	3,384	3,231	3,090	2,962	2,843	2,734	2,632	2,538	2,451	2,369	2,293	2,221	
53	4,208	3,986	3,787	3,606	3,442	3,293	3,156	3,030	2,913	2,805	2,705	2,612	2,524	2,443	2,367	
54	4,467	4,231	4,020	3,828	3,654	3,495	3,350	3,216	3,092	2,978	2,871	2,772	2,680	2,593	2,513	
55	4,904	4,646	4,414	4,203	4,012	3,838	3,678	3,531	3,395	3,269	3,152	3,044	2,942	2,847	2,759	
56	5,341	5,060	4,807	4,518	4,370	4,180	4,006	3,846	3,698	3,561	3,433	3,315	3,204	3,101	3,004	
57	5,778	5,474	5,200	4,952	4,727	4,521	4,333	4,160	4,000	3,852	3,714	3,586	3,466	3,355	3,250	
58	6,141	5,818	5,527	5,263	5,024	4,806	4,606	4,422	4,251	4,094	3,947	3,811	3,684	3,565	3,454	
59	6,503	6,161	5,853	5,574	5,320	5,089	4,877	4,682	4,502	4,335	4,180	4,036	3,902	3,776	3,658	
60	6,867	6,505	6,180	5,885	5,618	5,374	5,150	4,944	4,754	4,578	4,414	4,262	4,120	3,987	3,863	
61	7,297	6,912	6,567	6,254	5,969	5,710	5,472	5,254	5,051	4,864	4,690	4,529	4,378	4,236	4,104	
62	7,725	7,319	6,953	6,621	6,320	6,046	5,794	5,562	5,348	5,150	4,965	4,795	4,635	4,485	4,346	
63	8,154	7,725	7,339	6,989	6,671	6,381	6,116	5,871	5,645	5,436	5,242	5,061	4,892	4,734	4,587	
"B" (avg. in.)	8¼	8¾	9¼	9¾	10¾	10¾	11	11½	12	12¾	12¾	13¾	13¾	14¼	14¾	

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com



asc-es.com

Building connections that last™

Hanger Size No.	Total Travel* (IN); Load (LBS)																
	4	4½	5	5½	6	6½	7	7½	8	8½	9	9½	10	10½	11	11½	12
64	19,225	17,089	15,380	13,982	12,816	11,831	10,986	10,253	9,613	9,047	8,544	8,094	7,690	7,323	6,990	6,686	6,408
65	20,100	17,866	16,080	14,618	13,400	12,370	11,486	10,720	10,050	9,459	8,933	8,463	8,040	7,657	7,308	6,991	6,700
66	22,068	19,615	17,654	16,049	14,711	13,580	12,610	11,769	11,034	10,385	9,808	9,291	8,827	8,406	8,024	7,675	7,356
67	24,033	21,362	19,226	17,478	16,021	14,790	13,733	12,817	12,016	11,310	10,681	10,119	9,613	9,154	8,738	8,359	8,011
68	26,000	23,111	20,800	18,909	17,333	16,000	14,857	13,866	13,000	12,236	11,555	10,947	10,400	9,904	9,454	9,043	8,666
69	27,635	24,564	22,108	20,098	18,423	17,007	15,792	14,738	13,818	13,005	12,282	11,635	11,054	10,527	10,048	9,611	9,211
70	29,268	26,015	23,414	21,286	19,511	18,011	16,725	15,609	14,632	13,773	13,008	12,323	11,707	11,149	10,642	10,179	9,755
71	30,900	27,466	24,720	22,473	20,599	19,016	17,657	16,480	15,450	14,542	13,733	13,010	12,360	11,770	11,235	10,747	10,300
72	32,835	29,186	26,268	23,880	21,889	20,207	18,763	17,512	16,418	15,452	14,593	13,825	13,134	12,508	11,939	11,420	10,945
73	34,768	30,904	27,814	25,286	23,177	21,396	19,868	18,542	17,384	16,362	15,452	14,639	13,907	13,244	12,641	12,092	11,589
74	36,700	32,622	29,360	26,691	24,466	22,585	20,972	19,573	18,350	17,271	16,311	15,452	14,680	13,980	13,344	12,764	12,233
75	38,800	34,489	31,040	28,218	25,866	23,878	22,172	20,693	19,400	18,259	17,244	16,336	15,520	14,780	14,108	13,495	12,933
76	40,900	36,355	32,720	29,746	27,266	25,170	23,372	21,813	20,450	19,248	18,178	17,221	16,360	15,580	14,871	14,225	13,633
77	43,000	38,222	34,400	31,273	28,666	26,462	24,572	22,933	21,500	20,236	19,111	18,105	17,200	16,380	15,635	14,955	14,333
78	45,335	40,297	36,268	32,971	30,222	27,899	25,906	24,178	22,668	21,335	20,149	19,088	18,134	17,269	16,484	15,768	15,111
79	47,668	42,371	38,134	34,668	31,779	29,335	27,239	25,422	23,834	22,432	21,185	20,070	19,067	18,158	17,332	16,579	15,889
80	50,000	44,444	40,000	36,364	33,332	30,770	28,572	26,666	25,000	23,530	22,222	21,052	20,000	19,046	18,180	17,390	16,666
81	52,500	46,666	42,000	38,182	35,000	32,309	30,000	27,999	26,250	24,707	23,333	22,105	21,000	19,998	19,089	18,260	17,500
82	55,000	48,888	44,000	40,000	36,665	33,847	31,429	29,333	27,500	25,883	24,444	23,157	22,000	20,951	20,000	19,129	18,333
83	57,500	51,111	46,000	41,819	38,332	35,386	32,858	30,666	28,750	27,060	25,555	24,210	23,000	21,903	20,907	20,000	19,166
84			49,200	44,728	40,998	37,847	35,144	32,799	30,750	28,942	27,333	25,894	24,600	23,427	22,361	21,390	20,500
85			52,400	47,637	43,665	40,309	37,429	34,932	32,750	30,824	29,111	27,578	26,200	24,950	23,816	22,781	21,832
86			55,400	50,364	46,165	42,616	39,572	36,932	34,625	32,589	30,777	29,157	27,700	26,379	25,179	24,085	23,082
87			58,400	53,091	48,665	44,924	41,715	38,932	36,500	34,354	32,444	30,736	29,200	27,807	26,543	25,389	24,332
88			61,400	55,819	51,165	47,232	43,858	40,932	38,375	36,119	34,111	32,315	30,700	29,236	27,906	26,694	25,582
89			66,000	60,000	54,998	50,771	47,144	43,999	41,250	38,825	36,666	34,736	33,000	31,426	29,997	28,694	27,500
90					61,331	56,617	52,572	49,065	46,000	43,295	40,888	38,736	36,800	35,045	33,451	31,998	30,665
91					67,164	62,002	57,573	53,732	50,375	47,413	44,777	42,420	40,300	38,378	36,633	35,041	33,582
92					73,500	67,848	63,001	58,799	55,125	51,884	49,000	46,420	44,100	41,996	40,087	38,345	36,749
93					80,830	74,617	69,287	64,665	60,625	57,060	53,888	51,051	48,500	46,187	44,087	42,171	40,415
94					87,500	81,540	75,716	70,665	66,250	62,355	58,888	55,788	53,000	50,472	48,177	46,084	44,165
"B" dim Sizes 64 to 83	3½	4½	4½	5½	5½	6	6½	6½	7½	7½	8¼	8¼	9¼	9½	10½	10½	11
"B" dim Sizes 84 to 110			4¾	4¾	5	5¾	5¾	6¼	6¾	7¼	7½	7¾	8¾	8¾	9¾	9¾	10

Table continues on the following page.

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com



asc-es.com

Building connections that last™

Hanger Size No.	Total Travel* (IN); Load (LBS)																		
	4	4½	5	5½	6	6½	7	7½	8	8½	9	9½	10	10½	11	11½	12		
95							78,930	73,665	69,063	65,002	61,388	58,156	55,250	52,615	50,222	48,040	46,040		
96							82,145	76,665	71,875	67,649	63,888	60,525	57,500	54,757	52,268	50,000	47,915		
97							85,360	79,665	74,688	70,296	66,388	62,893	59,750	56,900	54,313	51,953	49,790		
98							87,500	82,665	77,500	72,943	68,888	65,261	62,000	59,043	56,358	53,909	51,665		
99								85,998	80,625	75,884	71,666	67,893	64,500	61,423	58,631	56,083	53,748		
100								87,500	83,750	78,826	74,444	70,524	67,000	63,804	60,903	58,257	55,831		
101									86,875	81,767	77,221	73,156	69,500	66,185	63,176	60,430	57,914		
102									87,500	84,708	80,000	75,787	72,000	68,566	65,448	62,604	60,000		
103										87,500	83,610	79,210	75,250	71,661	68,402	65,430	62,706		
104											87,221	82,629	78,500	74,756	71,357	68,256	65,414		
105												87,500	86,050	81,750	77,851	74,311	71,082	68,122	
106													87,500	85,000	80,946	77,265	73,908	70,831	
107														87,500	84,469	80,628	77,125	73,914	
108															87,500	83,992	80,342	77,000	
109																87,446	83,646	80,163	
110																	87,500	86,950	83,330
"B" dim Sizes 64 to 83	3⅝	4⅝	4⅝	5⅝	5½	6	6½	6⅞	7⅞	7⅞	8¼	8¼	9¼	9⅝	10⅝	10⅝	11		
"B" dim Sizes 84 to 110			4⅜	4⅜	5	5⅝	5⅜	6¼	6⅝	7⅜	7½	7⅞	8⅜	8¾	9⅝	9⅜	10		

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com



asc-es.com

Building connections that last™

Hanger Size No.	Total Travel* (IN); Load (LBS)															
	12½	13	13½	14	14½	15	15½	16	16½	17	17½	18	18½	19	19½	20
64	6,152	5,915	5,696	5,492	5,303	5,126	4,961	4,806								
65	6,432	6,184	5,955	5,742	5,544	5,359	5,187	5,025								
66	7,062	6,790	6,538	6,304	6,087	5,884	5,694	5,517								
67	7,690	7,394	7,120	6,966	6,629	6,408	6,201	6,008								
68	8,320	8,000	7,703	7,428	7,172	6,933	6,709	6,500								
69	8,843	8,503	8,188	7,895	7,623	7,369	7,131	6,909								
70	9,366	9,005	8,671	8,361	8,073	7,804	7,552	7,317								
71	9,888	9,507	9,155	8,828	8,523	8,239	7,973	7,725								
72	10,507	10,103	9,728	9,380	9,057	8,755	8,473	8,209								
73	11,126	10,697	10,301	9,932	9,590	9,270	8,971	8,692								
74	11,744	11,292	10,873	10,484	10,123	9,786	9,470	9,175								
75	12,416	11,938	11,496	11,084	10,703	10,346	10,012	9,700								
76	13,088	12,584	12,118	11,684	11,282	10,906	10,554	10,225								
77	13,760	13,230	12,740	12,284	11,861	11,466	11,096	10,750								
78	14,507	13,949	13,432	12,951	12,505	12,088	11,698	11,334								
79	15,254	14,666	14,123	13,618	13,149	12,710	12,300	11,917								
80	16,000	15,384	14,814	14,284	13,792	13,332	12,902	12,500								
81	16,800	16,153	15,555	14,998	14,482	14,000	13,547	13,125								
82	17,600	16,922	16,295	15,712	15,171	14,665	14,192	13,750								
83	18,400	17,692	17,036	16,427	15,861	15,332	14,837	14,375								
84	19,680	18,922	18,221	17,569	16,964	16,398	15,869	15,375								
85	20,960	20,153	19,406	18,712	18,068	17,465	16,902	16,375								
86	22,160	21,307	20,517	19,783	19,102	18,465	17,869	17,313								
87	23,360	22,461	21,628	20,855	20,136	19,465	18,837	18,250								
88	24,560	23,614	22,739	21,926	21,171	20,465	19,805	19,188								
89	26,400	25,384	24,443	23,569	22,757	21,998	21,288	20,626								
90	29,440	28,307	27,258	26,283	25,377	24,531	23,740	23,000								
91	32,240	31,000	29,850	28,782	27,791	26,864	25,998	25,188								
92	35,280	33,922	32,665	31,496	30,411	29,397	28,449	27,563								
"B" dim Sizes 64 to 83	11½	12	12¾	12⅞	13¾	13⅞	14¼	14¾	-	-	-	-	-	-	-	-
"B" dim Sizes 84 to 110	10¾	10⅞	11⅞	11⅝	12⅞	12½	12⅞	13⅞	13⅞	14⅞	14⅞	14⅞	15¾	15¾	16⅞	16⅞

Table continues on the following page.

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com



asc-es.com

Building connections that last™

Hanger Size No.	Total Travel* (IN); Load (LBS)															
	12½	13	13½	14	14½	15	15½	16	16½	17	17½	18	18½	19	19½	20
93	38,800	37,306	35,924	34,639	33,446	32,330	31,287	30,313								
94	42,400	40,768	39,257	37,583	36,549	35,330	34,190	33,125								
95	44,200	42,498	40,924	39,460	38,100	36,830	35,642	34,531	32,119	31,175	30,285	29,442	28,647	27,894	27,179	26,500
									33,482	32,498	31,570	30,691	29,863	29,078	28,332	27,625
96	46,000	44,230	42,590	41,067	39,652	38,330	37,093	35,938	34,845	33,822	32,856	31,941	31,080	30,262	29,486	28,750
97	47,800	45,960	44,257	42,673	41,204	39,829	39,545	37,344	36,209	35,145	34,141	33,191	32,295	31,446	30,640	29,875
98	49,600	47,690	45,923	44,280	42,755	41,329	40,000	38,750	37,572	36,468	35,427	34,441	33,511	32,631	31,794	31,000
99	51,600	49,613	47,775	46,066	44,479	42,996	41,609	40,313	39,087	37,939	36,855	35,830	34,862	33,946	33,076	32,250
100	53,600	51,536	49,627	47,851	46,203	44,662	43,221	41,875	40,602	39,409	38,284	37,219	36,214	35,262	34,358	33,500
101	55,600	53,459	51,479	49,637	47,927	46,329	44,834	43,438	42,117	40,880	39,712	38,607	37,565	36,578	35,640	34,750
102	57,600	56,382	53,330	51,422	49,651	47,995	46,447	45,000	43,632	42,350	41,141	39,996	38,916	37,894	36,922	36,000
103	60,200	57,882	55,738	53,744	51,892	50,162	48,544	47,031	45,602	44,262	42,998	41,801	40,673	39,604	38,588	37,625
104	62,800	60,382	58,145	56,065	54,134	52,328	50,640	49,063	47,571	46,174	44,855	43,607	42,429	41,315	40,255	39,250
105	65,400	62,882	60,552	58,386	56,375	54,495	52,737	51,094	49,541	48,085	46,712	45,412	44,186	43,025	41,921	40,875
106	68,000	65,382	62,960	60,707	58,616	56,661	54,834	53,125	51,510	50,000	48,569	47,218	45,943	44,736	43,588	42,500
107	70,960	68,228	65,700	63,350	61,168	59,127	57,220	55,438	53,752	52,173	50,683	49,273	47,942	46,683	45,485	44,350
108	73,920	71,074	68,441	65,992	63,719	61,594	59,607	57,750	55,994	54,350	52,797	51,328	49,942	48,630	47,383	46,200
109	76,960	74,000	71,255	68,706	66,340	64,127	62,059	60,125	58,297	56,585	54,969	53,439	52,000	50,630	49,331	48,100
110	80,000	76,920	74,070	71,420	68,960	66,660	64,510	62,500	60,600	58,820	57,140	55,550	54,050	52,630	51,280	50,000
"B" dim Sizes 64 to 83	11½	12	12¾	12⅞	13¾	13⅞	14¼	14¾	-	-	-	-	-	-	-	-
"B" dim Sizes 84 to 110	10¾	10⅞	11⅞	11⅝	12⅞	12½	12⅞	13⅞	13⅞	14⅞	14⅞	14⅞	15⅞	15¾	16⅞	16⅞

Table continues on the following page.

Shading in gray indicates this item is available upon request. For more information please visit www.asc-es.com

- (1) * Note: Total travel equals actual travel plus 1" or 20% (whichever is greater), rounded up to nearest ½" as applicable.
- (2) Constant supports are readily available for travel and load not listed in this table. Dimensions and lug locations may vary from those shown on the following pages.
- (3) For Type F Upthrust see page 213 for standard travel and sizes.
- (4) Fig. 80-V are not available for sizes 1 thru 9.



asc-es.com

Building connections that last™