


THREADED CAST BRONZE FITTINGS

ELBOWS – 90° REDUCING

CLASS 125#




Part No. LF Imp	Part No. LF Dom	Part No. Import	Part No. Domestic	Size	Pkg Qty	Approx Weight	A Inches	B Inches
	LF70102X01	P60102X01	P70102X01	1/4" x 1/8"	25	.08	0.65	0.60
	LF70103X01	P60103X01	P70103X01	3/8" x 1/8"	25	.13	0.75	0.78
	LF70103X02	P60103X02	P70103X02	3/8" x 1/4"	25	.13	0.75	0.78
	LF70104X02	P60104X02	P70104X02	1/2" x 1/4"	25	.19	1.78	1.68
	LF70104X03	P60104X03	P70104X03	1/2" x 3/8"	25	.19	.93	.90
	LF70106X02		P70106X02	3/4" x 1/4"	25	.47	1.00	1.00
	LF70106X03	P60106X03	P70106X03	3/4" x 3/8"	25	.47	0.97	0.97
LF60106X04	LF70106X04	P60106X04	P70106X04	3/4" x 1/2"	25	.47	1.08	1.11
	LF70110X02	P60110X02	P70110X02	1" x 1/4"	25	.50	0.97	1.38
LF60110X04	LF70110X04	P60110X04	P70110X04	1" x 1/2"	25	.50	1.20	1.24
LF60110X06	LF70110X06	P60110X06	P70110X06	1" x 3/4"	25	.50	1.30	1.31
	LF70112X04	P60112X04	P70112X04	1-1/4" x 1/2"	10	.60	1.25	1.37
	LF70112X06	P60112X06	P70112X06	1-1/4" x 3/4"	10	.60	1.39	1.48
	LF70112X10	P60112X10	P70112X10	1-1/4" x 1"	10	.60	1.52	1.60
	LF70114X04	P60114X04	P70114X04	1-1/2" x 1/2"	10	.93	1.84	1.84

THREADED CAST BRONZE FITTINGS

ELBOWS – 90° REDUCING CONT. (1)

CLASS 125#

Part No. LF Imp	Part No. LF Dom	Part No. Import	Part No. Domestic	Size	Pkg Qty	Approx Weight	A Inches	B Inches
	LF70114X06	P60114X06	P70114X06	1-1/2" x 3/4"	5	.93	1.50	1.75
	LF70114X10	P60114X10	P70114X10	1-1/2" x 1"	5	.93	1.55	1.72
LF60114X12	LF70114X12	P60114X12	P70114X12	1-1/2" x 1-1/4"	5	.93	1.72	1.81
LF60120X06	LF70120X06	P60120X06	P70120X06	2" x 3/4"	-	1.20	1.56	1.93
LF60120X10	LF70120X10	P60120X10	P70120X10	2" x 1"	-	1.20	1.56	1.93
LF60120X12	LF70120X12	P60120X12	P70120X12	2" x 1-1/4"	-	1.20	1.75	2.06
LF60120X14	LF70120X14	P60120X14	P70120X14	2" x 1-1/2"	-	1.20	1.89	2.07
	LF70124X20	P60124X20	P70124X20	2-1/2" x 2"	-	2.95	2.39	2.60
	LF70130X24		P70130X24	3" x 2-1/2"	-	4.36	2.83	2.99



DOMESTIC AND IMPORTED FITTINGS

Bronze Imported Threaded Fittings
ASTM B62

Alloy
C89833

Domestic Threaded Fittings
ASTM B584

Bronze Bar Stock Threaded Fittings
ASTM B16

Lead-Free Bronze Imported &
Domestic Threaded Fittings
ASTM B584

Alloy
C36000



(800) 257-9559

Fax: (866) 706-5260
sales@trentonpipe.com