


THREADED CAST BRONZE FITTINGS

TEES - REDUCING

CLASS 125#




Part No. LF Imp	Part No. LF Dom	Part No. Import	Part No. Domestic	Size	Pkg Qty	Approx Weight	A Inches	B Inches	C Inches
	LF72102X02X03		72102X02X03	1/4" x 1/4" x 3/8"	25	.19	0.78	0.78	0.75
	LF72103X03X02	62103X03X02	72103X03X02	3/8" x 3/8" x 1/4"	25	.19	0.75	0.75	0.78
	LF72103X03X04		72103X03X04	3/8" x 3/8" x 1/2"	25	.21	0.90	0.90	0.93
	LF72104X02X04		72104X02X04	1/2" x 1/4" x 1/2"	25	.25	1.84	1.84	0.84
	LF72104X03X03		72104X03X03	1/2" x 3/8" x 3/8"	25	.25	0.93	0.82	0.90
LF62104X04X02	LF72104X04X02	62104X04X02	72104X04X02	1/2" x 1/2" x 1/4"	25	.21	0.87	0.87	0.87
LF62104X04X03	LF72104X04X03	62104X04X03	72104X04X03	1/2" x 1/2" x 3/8"	25	.21	0.93	0.93	0.90
	LF72104X04X06	62104X04X06	72104X04X06	1/2" x 1/2" x 3/4"	25	.35	1.11	1.11	1.08
	LF72106X04X04	62106X04X04	72106X04X04	3/4" x 1/2" x 1/2"	10	.35	1.08	1.01	1.11
	LF72106X04X06	62106X04X06	72106X04X06	3/4" x 1/2" x 3/4"	10	.38	1.18	1.11	1.18
LF62106X06X02	LF72106X06X02	62106X06X02	72106X06X02	3/4" x 3/4" x 1/4"	25	.38	1.00	1.00	1.00
LF62106X06X04	LF72106X06X04	62106X06X04	72106X06X04	3/4" x 3/4" x 1/2"	10	.38	1.08	1.08	1.11
	LF72106X06X10	62106X06X10	72106X06X10	3/4" x 3/4" x 1"	10	.59	1.31	1.31	1.30
	LF72110X04X10	62110X04X10	72110X04X10	1" x 1/2" x 1"	10	.62	1.43	1.24	1.43
	LF72110X06X06	62110X06X06	72110X06X06	1" x 3/4" x 3/4"	10	.59	1.30	1.18	1.31

THREADED CAST BRONZE FITTINGS

TEES - REDUCING CONT. (1)


CLASS 125#



Part No. LF Imp	Part No. LF Dom	Part No. Import	Part No. Domestic	Size	Pkg Qty	Approx Weight	A Inches	B Inches	C Inches
	LF72110X06X10	62110X06X10	72110X06X10	1" x 3/4" x 1"	10	.62	1.43	1.31	1.43
LF62110X10X04	LF72110X10X04	62110X10X04	72110X10X04	1" x 1" x 1/2"	10	.62	1.20	1.20	1.24
LF62110X10X06	LF72110X10X06	62110X10X06	72110X10X06	1" x 1" x 3/4"	10	.62	1.30	1.30	1.31
	LF72110X10X12	62110X10X12	72110X10X12	1" x 1" x 1-1/4"	10	.81	1.60	1.60	1.52
	LF72110X10X14	62110X10X14	72110X10X14	1" x 1" x 1-1/2"	10	1.15	1.72	1.72	1.55
	LF72112X04X12	62112X04X12	72112X04X12	1-3/4" x 1/2" x 1-3/4"	10	.89	1.69	1.40	1.69
	LF72112X06X06	62112X06X06	72112X06X06	1-3/4" x 3/4" x 3/4"	10	.81	1.37	1.25	1.50
	LF72112X06X12	62112X06X12	72112X06X12	1-3/4" x 3/4" x 1-3/4"	10	.89	1.69	1.48	1.69
LF62112X12X04	LF72112X12X04	62112X12X04	72112X12X04	1-3/4" x 1-3/4" x 1/2"	5	1.15	1.81	1.81	1.72
LF62112X12X06	LF72112X12X06	62112X12X06	72112X12X06	1-3/4" x 1-3/4" x 3/4"	10	.89	1.39	1.39	1.48
LF62112X12X10	LF72112X12X10	62112X12X10	72112X12X10	1-3/4" x 1-1/4" x 1"	5	.89	1.52	1.52	1.60
	LF72112X12X14	62112X12X14	72112X12X14	1-3/4" x 1-3/4" x 1-1/2"	5	1.15	1.81	1.81	1.72
	LF72114X04X14	62114X04X14	72114X04X14	1-1/2" x 1/2" x 1-1/2"	5	1.14	1.81	1.56	1.81
	LF72114X06X14	62114X06X14	72114X06X14	1-1/2" x 3/4" x 1-1/2"	5	1.14	1.84	1.60	1.84
	LF72114X10X14	62114X10X14	72114X10X14	1-1/2" x 1" x 1-1/2"	-	1.14	1.87	1.81	1.87

THREADED CAST BRONZE FITTINGS

TEES REDUCING CONT. (2)



Part No. LF Imp	Part No. LF Dom	Part No. Import	Part No. Domestic	Size	Pkg Qty	Approx Weight	A Inches	B Inches	C Inches
LF62114X14X04	LF62114X14X04	62114X14X04	72114X14X04	1-1/2" x 1-1/2" x 1/2"	5	1.14	1.32	1.32	1.53
LF62114X14X06	LF72114X14X06	62114X14X06	72114X14X06	1-1/2" x 1-1/2" x 3/4"	5	1.14	1.42	1.42	1.60
LF62114X14X10	LF72114X14X10	62114X14X10	72114X14X10	1-1/2" x 1-1/2" x 1"	5	1.14	1.55	1.55	1.72
LF62114X14X12	LF72114X14X12	62114X14X12	72114X14X12	1-1/2" x 1-1/2" x 1-1/4"	5	1.14	1.72	1.72	1.81
	LF72120X06X20	62120X06X20	72120X06X20	2" x 3/4" x 2"	-	1.78	2.12	2.84	2.12
	LF72120X14X20	62120X14X20	72120X14X20	2" x 1-1/2" x 2"	-	1.78	2.12	2.07	2.12
LF62120X20X04	LF72120X20X04	62120X20X04	72120X20X04	2" x 2" x 1/2"	-	1.78	1.50	1.50	1.87
LF62120X20X06	LF72120X20X06	62120X20X06	72120X20X06	2" x 2" x 3/4"	-	1.78	1.47	1.47	1.84
LF62120X20X10	LF72120X20X10	62120X20X10	72120X20X10	2" x 2" x 1"	5	1.78	1.59	1.59	1.95
LF62120X20X12	LF72120X20X12	62120X20X12	72120X20X12	2" x 2" x 1-1/4"	-	1.78	1.77	1.77	2.04
LF62120X20X14	LF72120X20X14	62120X20X14	72120X20X14	2" x 2" x 1-1/2"	-	1.78	1.89	1.89	2.07
	LF72124X14X24	62124X14X24	72124X14X24	2-1/2" x 1-1/2" x 2-1/2"	-	2.66	2.06	2.50	2.69
		62124X24X20		2-1/2" x 2-1/2" x 2"	-	2.66	2.39	2.39	2.60
	LF72130X30X20	62130X30X20	72130X30X20	3" x 3" x 2"	-	4.77	2.52	2.52	2.89
		62130X30X24		3" x 3" x 2-1/2"	-	4.77	2.83	2.83	2.99

DOMESTIC AND IMPORTED FITTINGS

Bronze Imported Threaded Fittings
ASTM B62

Domestic Threaded Fittings
ASTM B584

Lead-Free Bronze Imported &
Domestic Threaded Fittings
ASTM B584

Alloy
C89833

Bronze Bar Stock Threaded Fittings
ASTM B16

Alloy
C36000



(800) 257-9559

Fax: (866) 706-5260

sales@trentonpipe.com