


RH & LH Corner Connector Figs. AS 2128, AS 922, AS 2128, AS 665, AS 667




Description

Anvil-Strut Wing Fittings are designed to fit with all Anvil-Strut 1 5/8" wide channels. Unless otherwise noted, Anvil-Strut Wing Fittings are manufactured from 1/4" thick carbon steel, 1 5/8" wide, all holes are 9/16" diameter, spaced 1 7/8" on center and 13/16" from the end.

RH & LH 2-Hole Single Corner Angle Connector


AS 922 EG, GR ZTC



When ordering, Specify RH or LH
Std Pkg 20 – Wt/100 pcs: 60 Lbs.

RH & LH 6-Hole Corner Connector

AS 2128 EG, GR



When ordering, Specify RH or LH
Std Pkg 10 – Wt/100 pcs: 119 Lbs.

Page notes unless otherwise specified: 1/4" thick, 1 5/8" wide, holes 9/16" diameter, spaced 1 7/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum
HG: Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel
ZTC: Zinc Trivalent Chromium Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

RH & LH Corner Connector Figs. AS 2128, AS 922, AS 2128, AS 665, AS 667

4-Hole Double Corner Connector


AS 665 EG, GR ZTC



Std Pkg 25 - Wt/100 pcs: 76 Lbs.

8-Hole Double Corner Connector

AS 667 EG, GR ZTC



Std Pkg 10 - Wt/100 pcs: 155 Lbs.

Page notes unless otherwise specified: 1/4" thick, 1 5/8" wide, holes 9/16" diameter, spaced 1 7/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum
HG: Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel
ZTC: Zinc Trivalent Chromium Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.