


Six Hole Double Corner Connector Fig. AS 666, AS 923, AS 913, AS 668, AS 821, AS 669




Description

Anvil–Strut Wing Fittings are designed to fit with all Anvil–Strut $1^5/8$ " wide channels. Unless otherwise noted, Anvil–Strut Wing Fittings are manufactured from 1/4" thick carbon steel, $1^5/8$ " wide, all holes are 9/16" diameter, spaced $1^7/8$ " on center and $1^3/16$ " from the end.

5-Hole Two Angle Connector


AS 923 EG, GR, ZTC



Std Pkg 25 - Wt/100 pcs: 93 Lbs.

10-Hole Two Angle Clevis Connector

AS 913 EG, GR, ZTC



Std Pkg 10 - Wt/100 pcs: 193 Lbs.

Page notes unless otherwise specified: $\frac{1}{4}$ " thick, $1^5/8$ " wide, holes $\frac{9}{16}$ " diameter, spaced $1^7/8$ " on center and $\frac{13}{16}$ " from end.

LEGEND:

GR: Powder Coated Supr-Green EG: Electro-Galvanized PG: Pre-Galvanized AL: Aluminum HG: Hot Dipped Galvanized PL: Plain SS: Stainless Steel

ZTC: Zinc Trivalent Chromium Stainless Steel (SS), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	



Six Hole Double Corner Connector Fig. AS 666, AS 923, AS 913, AS 668, AS 821, AS 669

6-Hole Three Angle Connector

GR,

ZTC

EG,


AS 668

53/8"

Std Pkg 10 - Wt/100 pcs: 113 Lbs.

8-Hole Double Angle Connector


AS 821 EG, GR, ZTC



Std Pkg 10 - Wt/100 pcs: 113 Lbs.

12-Hole Three Angle Clevis Connector


AS 669 EG, GR, ZTC



Std Pkg: 10 - Wt/100 pcs: 230 Lbs.

6-Hole Double Corner Connector

AS 666 EG, GR, ZTC



Std Pkg 25 - Wt/100 pcs: 115 Lbs.

Page notes unless otherwise specified: 1/4" thick, 15/8" wide, holes 9/16" diameter, spaced 17/8" on center and 13/16" from end.

LEGEND:

GR: Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum **HG:** Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel

ZTC: Zinc Trivalent Chromium Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes. Pricing is located in the Specialty Strut Section of the Anvil–Strut price book.

