


## AS 2623 Swivel Adapter Figs. AS 2623, AS 2654, AS 871, AS 684




### Description

Anvil-Strut Beam Clamps are designed to secure all Anvil-Strut 1 $\frac{5}{8}$ " wide channels, or threaded rod, to beams or supports for the purpose of running piping, conduit or tubing.

For additional Anvil Beam Clamps, refer to the Pipe Hangers and Hardware Section of the website or the Anvil Pipe Hangers and Supports Catalog.

### Column Attachment

AS 2654 EG, GR




Catalog No.	Use With	Wt./100 Pcs.
AS 2654	AS 200	53 (pair)

Sold only in pairs  
Std Pkg 25 - Wt/100 pcs: See chart above.

### Safety Anchor Strap

AS 871 EG



A	Wt./100 Pcs.
9"	33
12"	48
15"	57

(For Heavy Duty Beam Clamps.) Use with AS 858, AS 865 (Cannot Be Used With  $\frac{5}{8}$ " Rod Size Beam Clamps and Larger).  
Std Pkg: Bulk - Wt/100 pcs: See chart above.

#### LEGEND:

**GR:** Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum  
**HG:** Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel **ZTC:** Zinc Trivalent Chromium  
Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes.  
Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

## AS 2623 Swivel Adapter Figs. AS 2623, AS 2654, AS 871, AS 684

### Beam Clamp


AS 684 EG, GR



Set Screw included  
Std Pkg 25 - Wt/100 pcs: 92 Lbs.

### Swivel Adapter

AS 2623 EG



Use With AS 2622 Beam Clamp.  
Std Pkg: 50 - Wt/100 pcs: 31 lbs.

#### LEGEND:

**GR:** Powder Coated Supr-Green **EG:** Electro-Galvanized **PG:** Pre-Galvanized **AL:** Aluminum  
**HG:** Hot Dipped Galvanized **PL:** Plain **SS:** Stainless Steel **ZTC:** Zinc Trivalent Chromium  
Stainless Steel (**SS**), Zinc Trivalent Chromium (**ZTC**) and Hot Dipped Galvanized (**HG**) are specialty finishes.  
Pricing is located in the Specialty Strut Section of the Anvil-Strut price book.