



DIMENSION	1/4"-3/8"-1/2"	3/4"	1"	1-1/4"	1-1/2"	2"	2-1/2"	3"
A (SR)	7-5/8"	8"	9"	9-1/2"	10-1/2"	11-5/8"	13"	14-3/4"
A (DA)	7-5/8"	8"	8-1/4"	9-1/2"	10"	10-3/4"	13"	14"
B (SR)	7-3/4"	7-3/4"	8-1/4"	8-1/4"	10"	10"	10"	14-1/2"
B (DA)	5-3/4"	5-3/4"	5-3/4"	6"	6"	6"	7-1/4"	7-1/4"
C (SR)	4-5/8"	4-3/4"	5-1/4"	5-1/2"	6-1/4"	6-5/8"	7-1/2"	8-3/8"
C (DA)	4-5/8"	4-3/4"	4-7/8"	5-1/2"	5-3/4"	6-1/8"	7-1/2"	8"
D	5/8"	7/8"	1"	1-1/4"	1-1/2"	1-7/8"	2-1/4"	2-3/4"
E	3"	3"	3"	3"	3"	3"	3"	3"
F (SR)	1-5/16"	1-5/16"	1-3/4"	1-3/4"	2-1/8"	2-1/8"	2-1/8"	2-1/2"
F (DA)	1-5/16"	1-5/16"	1-5/16"	1-3/4"	1-3/4"	1-3/4"	2-1/8"	2-1/8"
G (SR)	1-7/8"	1-7/8"	2"	2"	2-1/2"	2-1/2"	2-1/2"	3"
G (DA)	1-7/8"	1-7/8"	1-7/8"	2"	2"	2"	2-1/2"	2-1/2"
H (SR)	3-1/4"	3-1/4"	3-3/8"	3-3/8"	3-7/8"	3-7/8"	3-7/8"	4-3/8"
H (DA)	3-1/4"	3-1/4"	3-1/4"	3-3/8"	3-3/8"	3-3/8"	3-7/8"	3-7/8"
J (SR)	2-5/8"	2-5/8"	3-1/2"	3-1/2"	4-1/4"	4-1/4"	4-1/4"	5"
J (DA)	2-5/8"	2-5/8"	2-5/8"	3-1/2"	3-1/2"	3-1/2"	4-1/4"	4-1/4"
K	2-5/8"	3"	3-1/2"	4"	4-1/2"	5"	6-5/8"	7-1/4"

NOTE: "H" IS CENTERLINE TO OUTSIDE SURFACE OF SOLENOID-

Series S1-SS with C-Series Pneumatic Actuator

