

Adjustable Swivel Ring, Split Ring Type Fig. 104




Fig. 104: Dimensions (in) • Loads (lbs) • Weight (lbs)

Pipe Size	Max Load	Weight	Rod Size A	B	C	D	E	Inside Dia. of Ring - F
¾		0.31			2 ³ / ₈	3 ⁷ / ₁₆	1 ¹⁵ / ₁₆	1 ³ / ₁₆
1		0.32		2 ⁷ / ₈	2 ¹ / ₄	3 ⁹ / ₁₆	1 ³ / ₄	1 ⁷ / ₁₆
1¼	300	0.34	¾	3	2 ³ / ₁₆	3 ⁷ / ₈	1 ¹¹ / ₁₆	1 ¹³ / ₁₆
1½		0.41		3 ³ / ₈	2 ³ / ₁₆	4 ¹ / ₈		2 ¹ / ₁₆
2		0.48		3½	2 ⁵ / ₁₆	4 ¹¹ / ₁₆	1 ¹³ / ₁₆	2½
2½		0.58		3 ¹⁵ / ₁₆	2½	5 ³ / ₈	1 ⁷ / ₈	3
3	500	1.00	½	4 ³ / ₈	2 ⁵ / ₈	6 ¹ / ₈	2	3¾
4	900	1.70	5 ⁵ / ₈	5 ¹³ / ₁₆	3 ⁹ / ₁₆	8 ¹ / ₁₆	2 ⁷ / ₈	4 ¹³ / ₁₆
6	1,300	3.80	¾	7 ⁵ / ₈	4 ⁵ / ₁₆	10 ¹⁵ / ₁₆	3½	7 ¹ / ₁₆

Size Range

¾" through 6"

Materials

Malleable Iron, Carbon Steel

Finish

Plain or

Zinc Plated (Hot-Dip Galvanized optional)

Service

Recommended for suspension of non-insulated stationary pipe lines

Maximum Temperature

450 °F

Approvals

Complies with Federal Specification A-A-1192A (Type 6), WW-H-171-E (Type 6), ANSI/MSS SP-69 and MSS SP-58 (Type 16)

Features

- Labor-saving features in installation completely outweigh slight additional cost
- Hanger may be installed prior to suspension of pipe
- Off-center hinge provides seating for pipe during installation
- Wedge-type locking pin is inseparably cast into hinged section, sizes 2½" and larger
- Adjustable swivel ring is self-locking; prevents loosening due to vibration; maintains proper pitch of pipe
- Wire retaining ring prevents separation of swivel shank from pipe ring before installation

Ordering

Specify pipe size, figure number, name and finish



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	