

Heavy Duty Beam Clamp Fig. 134



Size Range: 4" through 12"

Material: Carbon Steel

Finish: Plain or Hot-Dip Galvanized with Zinc Plated Fasteners

Service: Clamp centers the load on beam to prevent distortion.


Approvals: Complies with Federal Specification A-A-1192A (Type 21) WW-H-171-E (Type 21), ANSI/MSS SP-69 and MSS SP-58 (Type 21). Fig. 134 UL Listed and FM Approved when used with 1/2" and 5/8" rod.

Components:

Two half-clamps, pipe spacer and bolt with nut assembled.

Ordering: Figure number, width of flange, name and finish.

Note: Spacer is furnished for use with Fig. 290 weldless eye nuts. Spacer may be removed for use with Fig 278 eye rods.



Flange Size

Flange Width	Max Flange Thickness	Weight (lbs)
		Fig. 134 Heavy Duty
4	1/2	3.82
5	5/8	4.35
6	3/4	4.52
7	7/8	4.84
8		5.10
9	1	5.83
10		6.25
11		6.67
12		7.09

Fig. 134: Dimensions (in) • Loads (lbs)

	C	B	Bolt Size	Spacer O.D.	Max Load
Fig. 134	3/4	2 1/4	5/8	1 1/16	3,000



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	