Anvil[®] Rod Couplings & Turnbuckles



Rod Coupling Fig. 136: Straight Fig. 136R: Reducing







Description

Size Range ¹/₄" through 1"

Material Malleable iron

Finish

Plain or Zinc Plated

Service

For connecting rod lengths within limitation.

Approvals

Fig. 136: UL, ULC Listed $(^{3}/_{8}" - ^{7}/_{8}" \text{ rod size})$ and FM Approved $(^{3}/_{8}" \text{ and } ^{1}/_{2}" \text{ rod size})$. Fig. 136R: UL Listed $(^{1}/_{2}" \text{ and } ^{3}/_{8}" \text{ rod size})$.

Ordering

Specify rod tapping size, figure number and name. Furnished with right-hand UNC threads only.

Features

- Available in reducing sizes
- Provides visual inspection of thread engagement
- Uniform strength; good appearance




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

Anvil[®] Rod Couplings & Turnbuckles



Rod Coupling Fig. 136: Straight Fig. 136R: Reducing



Dimensions (In) • Loads (Lbs) • Weights (Lbs)

Rod Size A	Max Load	Weight	L	D
traight: Fig. 136				
1/4	230	0.06	13⁄8	⁵ /8
3/8	730	0.10	15⁄8	¹¹ / ₁₆
1/2	1,350	0.20	21/8	15/16
⁵ /8	2,160	0.33	21/2	11/8
3/4	3,230	0.44	25/8	11⁄4
7/8	4,480	0.96	33/16	15⁄8
1	5,900	0.94	23/4	1 ¹³ /16
Reducing: Fig. 136R				
¹ / ₂ X ³ / ₈	730	0.21	21/8	21/8



asc-es.com

Building connections that last "