

Threaded Safety Valve Discharge Elbow





Anvil standard and extra heavy cast iron threaded fittings are manufactured in accordance with ASME-B16.4 (except plugs and bushings, ASME B16.14). Dimensions also conform to Federal Specifications, WW-P-501 (except plugs and bushings WW-P-471).

Cast iron threaded fittings are available in both black and galvanized.

For Listings/Approval Details and Limitations, visit our website at www.asc−es.com or contact an ASC Engineered Solutions™ Representative.

See following page for standards and specifications.

Cast Iron Threaded Fittings Pressure - Temperature Ratings

| _ | Pres | ssure | | Pressure | | |
|--------------|-----------|-----------|-------------|-----------|-----------|--|
| Temperature | Class 125 | Class 250 | Temperature | Class 125 | Class 250 | |
| °F/°C | PSI/bar | PSI/bar | °F/°C | PSI/bar | | |
| -20°-150° | O° 175 4 | | 300° | 140 | 310 | |
| -28.9°-65.6° | 12.1 | 27.6 | 148.9° | 9.7 | 21.4 | |
| 200° | 165 | 370 | 350° | 125 | 300 | |
| 93.3° | 11.4 | 25.5 | 176.7° | 8.6 | 20.7 | |
| 250° 150 | | 340 | 400° | _ | 250 | |
| 121.1° | 10.3 | 23.4 | 204.4° | _ | 17.2 | |

Note:

Anvil standard and extra heavy cast iron threaded fittings are manufactured in accordance with ASME B16.4. Plugs and bushings are manufactured in accordance with ASME B16.14.

Figure 367 Concentric Reducers do not meet the overall length requirement of ASME B16.4. All other dimensions are in compliance.



| PROJECT INFORMATION | APPROVAL STAMP |
|---------------------|-------------------|
| Project: | Approved |
| Address: | Approved as noted |
| Contractor: | Not approved |
| Engineer: | Remarks: |
| Submittal Date: | |
| Notes 1: | |
| Notes 2: | |



Threaded Safety Valve Discharge Elbow **Fig. 1538**



Standards and Specifications

Cast Iron Threaded Fittings

| | Dimensions | Material | Galvanizing* | Thread | Pressure Ratin |
|-----------|------------|---------------|--------------|--------------|----------------|
| Class 125 | ASME B16.4 | ASTM A126 (A) | ASTM A153 | ASME B1.20.1 | ASME B16.4 |
| Class 250 | ASME B16.4 | ASTM A126 (A) | ASTM A153 | ASME B1.20.1 | ASME B16.4 |

Cast Iron Plugs and Bushings

| Dimensions | | Galvanizing* | Thread | Pressure Rating |
|-------------|---------------|--------------|--------------|-----------------|
| ASME B16.14 | ASTM A126 (A) | ASTM A153 | ASME B1.20.1 | ASME B16.14 |

Note



asc-es.com


Building connections that last™

^{*} ASTM B633. Type I, SC 4, may be supplied as alternate zinc coating per applicable ASME B16 product standard.



Threaded Safety Valve Discharge Elbow **Fig. 1538**





| Elbow Pipe Size | Riser Pipe Size | В | С | D | E | F | G | н | J | K | L | Unit Weight |
|--------------------|--------------------|---------|--------|--------|--------|---------|--------|--------|--------|--------|--------|----------------|
| | Α | | | | | | | | | | | Black |
| NPS/DN | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | In./mm | Lbs./kg |
| 21/2 | 31/2 | 2 11/16 | 45/16 | 81/2 | 15/8 | 1 15/16 | 21/8 | 23/4 | 3/4 | - | - | 12.00 |
| 65 | 89 | 89 | 110 | 216 | 41 | 49 | 54 | 70 | 19 | | | 5.44 |
| 3 | 4 | 31/8 | 47/8 | 91/2 | 15/8 | 25/16 | 29/16 | 31/8 | 3/4 | _ | _ | 15.00 |
| 80 | 102 | 79 | 124 | 241 | 41 | 59 | 65 | 79 | 19 | | | 6.80 |
| 4 | 5 | 33/4 | 53/4 | 11 | 13/4 | 215/16 | 33/16 | 33/4 | 3/4 | _ | _ | 27.00 |
| 100 | 127 | 95 | 146 | 279 | 44 | 75 | 81 | 95 | 19 | - | - | 12.24 |

Note:


See first page for pressure-temperature ratings.

Following are the advantages of Anvil safety valve discharge elbow for piping connections to safety valves when attached to boilers, etc.:

- Drip pan for removing condensate and rain water casts integral with elbow.
- · Strains on safety valve minimized.
- Pipe tap J is standard.

With multiple pop safety valve, leakage of vapor at any discharge elbow indicates valve in operation.

Street elbows and flanged elbows furnished on order.





asc-es.com

Building connections that last™



Fig. 1538 Threaded Safety Valve Discharge Elbow

General Assembly of Threaded Fittings

1 Inspect both male and female components prior to assembly.

- Threads should be free from mechanical damage, dirt, chips and excess cutting oil.
- Clean or replace components as necessary.

2 Application of thread sealant

- Use a thread sealant that is fast drying, sets-up to a semi hard condition and is vibration resistant. Alternately, an anaerobic sealant may be utilized.
- Throroughly mix the thread sealant prior to application.
- · Apply a thick even coat to the male threads only. Best application is achieved with a brush stiff enough to force sealant down to the root of the threads.

3 Joint Makeup

- For sizes up to and including 2" pipe, wrench tight makeup is considered three full turns past handtight. Handtight engagement for ½" through 2" thread varies from 4½ turns to 5 turns.
- For 2½" through 4" sizes, wrench tight makeup is considered two full turns past handtight. Handtight engagement for 2½" through 4" thread varies from 5½ turns to 6¾ turns.



asc-es.com

Building connections that last™