


Rib-Lok Shield Fig. 168

Discontinued product,
Please see Fig. 167



Shield Size Selection for Nominal Pipe Size

Pipe Size	Insulation Thickness (in)				
	1/2	3/4	1	1 1/2	2
1/2			-	-	-
3/4	1	1	2	4	6
1		2	3	5	
1 1/4		3	3	6	7
1 1/2			4		
2	3	4	5	7	8
2 1/2	4	5	6		
3	5	6	7	8	9
3 1/2			8	9	10
4					
5	-	-	9	10	11
6			10	11	12
8			12	13	14

Shield Size Selection for Copper Tubing

Tube Size	Insulation Thickness (in)				
	1/2	3/4	1	1 1/2	2
3/8					
1/2, 5/8		1	2	3	5
1		1	2	4	6
1 1/4	1	2	3	5	7
1 1/2	2	3	4	6	
2	3	4	5	7	8
2 1/2	4	5	6		
3	5	6	7	8	9
3 1/2	6	7			
4	7	7	8	9	10
5	8	8	9	10	11
6	9	9	10	11	12
8	11	11	12	13	14

Size Range: 1/2" through 8" pipe or copper tube with up to 2" insulation

Material: Carbon Steel

Finish: Pre-Galvanized Material

Approvals: Complies with Federal Specification A-A-1192A (Type 40), WW-H-171-E (Type 41), ANSI/MSS SP-69 and MSS SP-58 (Type 40).

Service: To be used with Fig. 65 or Fig. 260 clevis. Designed to prevent damage to insulation by hanger. Ribs keep shield centered in hanger.

How to size: Refer to shield size selection table below.

Ordering: Specify size, figure number and name.

Note: Data applicable to shields for thicker insulation or larger pipe size is available upon request.




Fig. 168: Dimensions (in) • Weight (lbs)

Shield Size	Max O.D. of Insulation	Stock Sizes	Weight	Fig. 260
1	2 3/8		0.41	2
2	2 7/8		0.50	2 1/2
3	3 1/2		0.61	3
4	4		0.69	3 1/2
5	4 1/2	18 ga. x 8	0.78	4
6	5		0.99	5
7	5 5/8		1.09	5
8	6 5/8		1.28	6
9	7 5/8		1.51	8
10	8 5/8		2.24	8
11	9 5/8		2.48	10
12	10 3/4	18 ga. x 12	2.76	10
13	11 3/4		3.03	12
14	12 3/4		3.28	12

Shading in gray indicates this shield fits loosely inside the Fig. 260. To be used properly, the Fig. 260 requires a spacer.

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	