
# Adjustable Side Beam Clamp **Fig. 14**





## **Material Specifications**

Size Range <sup>3</sup>/<sub>8</sub>" through <sup>5</sup>/<sub>8</sub>"

#### Material

Carbon Steel

#### Finish

Plain

Zinc Plated

#### Service

Recommended for supporting pipe from the bottom flange of beams.

#### Approvals

Complies with Federal Specification A-A-1192A (Type 27), WW-H-171-E (Type 54), ANSI/MSS SP-69 and MSS SP-58 (Type 27).

#### Ordering

Specify rod size, figure number, name and finish.

### Dimensions (In) - Load (Lbs) - Weight (Lbs)

Rod Size A	Max Load	Hole Size A	Adjustment Beam Width		Weight
			Min.	Max.	rreight
In.	Lbs.	In.	In.	ln.	Lbs.
3/8	300	7/16			1.19
1/2	700	<sup>9/</sup> 16	31/2	8	1.67
5/8	1000	<sup>11</sup> / <sub>16</sub>			2.23



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	