


Steel Side Beam Bracket Fig. 206 (formerly Afcon Fig. 556/560/565)



Material Specifications

Size Range

3/8" through 5/8"

Material

Carbon steel

Finish

Plain

Zinc Plated (Hot-Dip Galvanized optional)

Service

Clip can be fastened to side of joist or wall to support hanger rod.

Approvals

Complies with Federal Specification A-A-1192A (Type 34), WW-H-171-E (Type 35), ANSI/MSS SP-69 and MSS SP-58 (Type 34).
UL Listed and FM Approved (steel beam only).

Ordering

Specify rod size, figure number, name and finish.

Dimensions (In) - Load (Lbs) - Weight (Lbs)

Rod Size A	Max Load		Weight	L	B	Hole Size H	T
	With Lag Screw	With Bolt to Steel					
In.	Lbs.	Lbs.	Lbs.	In.	In.	In.	In.
3/8	650	1,150	0.44	2 1/16	5/8	7/16	1/4
1/2			0.43			9/16	
5/8	850	2,000	0.84	2 1/2	3/4	1 1/16	3/8



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	