


Eye Rod Not Welded

Fig. 248: (Formerly Afcon Fig. 680): Right Hand Threads

Fig. 248L: Left Hand Threads



Description

Size Range
3/8" through 2 1/2"

Material
Carbon steel

Finish
Plain or
Zinc Plated

Maximum Temperature
650° F

Ordering
Specify rod diameter, figure number, name, rod length and finish. Specify thread length if other than standard.

Features:

Through 1 1/2", inside diameter of eye will accommodate a bolt diameter 1/8" larger than rod diameter; 1 3/4" and larger, inside diameter of eye will take a bolt diameter 1/4" larger than rod diameter.

Note: The acceptability of galvanized coatings at temperatures above 450°F is at the discretion of the end user.




PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

Eye Rod Not Welded

Fig. 248: (Formerly Afcon Fig. 680): Right Hand Threads

Fig. 248L: Left Hand Threads



Dimensions (In) • Loads (Lbs)

Rod Size A	Standard Rod Thread Length - D	L (min)	Max Load 650° F
3/8	2 1/2	4 1/4	240
1/2			
5/8	3	4 1/2	705
3/4			
7/8	3 1/2	6 1/2	1,470
1	4	7 1/4	1,940
1 1/4	5	8 1/4	3,120
1 1/2	6	10	4,650
1 3/4	7	12	6,380
2	8	14	8,280
2 1/4	9	15 1/2	10,900
2 1/2	10	17	13,400



asc-es.com

Building connections that last™