

Pipe Saddle Support with U-Bolt Fig. 259

Size Range: 4" through 36" pipe

Material: Cast iron stanchion saddle with steel yoke and nuts. 14" through 36" carbon steel saddle with steel yoke. 4" through 12" steel saddle available on special request.

Finish: Plain or Hot-Dip Galvanized with EG U-bolt and hardware. Available in all HDG finish upon special request.

Service: Stanchion type support with additional stability provided by U-bolt attachment to pipe.

Approvals: Complies with Federal Specification A-A-1192A (Type 37), ANSI/MSS SP-69 and MSS SP-58 (Type 37).

Installation: Same as pipe saddle support Fig. 258, except that yoke is attached to saddle after pipe is in place.

Features: U-bolt yoke provides stability.

Ordering: Specify pipe size to be supported, figure number, name, material and finish.

Order Separately: Figure 63P Square Cut End Stanchion. Specify "H" and pipe size to be supported by Figure 259.




Fig. 259 Cast Iron




Fig. 259 Fabricated Steel

Fig. 259: Dimensions (in) • Weight (lbs)

Pipe Size	Weight	A	B Cast	B Fabricated	C Cast	C Fabricated	Max Load
4	10.8		4 ³ / ₁₆	3 ⁵ / ₈			
5	12.1		4 ¹³ / ₁₆	4 ¹ / ₈			
6	12.7		5 ⁷ / ₁₆	4 ¹¹ / ₁₆			
8	21.3	3	6 ¹⁵ / ₁₆	6 ¹¹ / ₁₆	3 ⁵ / ₈	4	3,800
10	25.7		8 ⁷ / ₁₆	7 ³ / ₄			
12	31.2		9 ¹⁵ / ₁₆	8 ³ / ₄			
14	28.0			10 ¹ / ₂			
16	31.0			11 ¹ / ₂			5,300
18	40.0			13 ¹ / ₂			6,700
20	43.0			14 ¹ / ₂			
22	46.0			15 ¹ / ₂			
24	52.0	4	--	17 ¹ / ₂	--	6	7,300
26	55.0			18 ¹ / ₂			
30	69.0			20 ⁵ / ₈			
32	73.0			21 ⁵ / ₈			
36	81.0			23 ⁵ / ₈			




Fig. 63, Type P
Square Cut End for use with
Figure 258 or 259 Pipe
Saddle Support

*Standard Wall Pipe.

The above load ratings are applicable to the saddle only and are not applicable to the stanchion or other means used to support the saddle.

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	