SPF Cast Iron Threaded Fittings



Class 125 (Standard) Fig. 3351 90° Elbow







For Listings/Approval Details and Limitations, visit our website at www.asc-es.com or contact an ASC Engineered Solutions[™] Sales Representative.

Material Specifications

Dimensions: ASME B16.4 Class 125

Material: ASTM A126

Finish: Black or Hot Dip Galvanized per


ASTM A153 Class A


Threads: NPT per ASME B1.20.1

Agency Approvals: All cast iron threaded fittings are UL/ULC Listed and FM Approved.

Figure 3351 90° Elbow

Nominal Size	Maximum Working Pressure ▲	Dimension A	Approx Wt. Each
In. (mm)	psi (kPa)	In. (mm)	Lbs. (kg)
1	300	1.50	0.84 0.38
25	2065	38.10	
1½	300	1.75	1.34 0.61
32	2065	44.45	
1½	300	1.94	1.80
40	2065	49.27	0.82
2	300	2.25	2.90
50	2065	57.15	1.32
2½	300	2.70	4.75
65	2065	68.58	2.15







PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	