


Strap Short Fig. 262



Size Range: 1/2" through 4"
Material: Carbon steel
Finish: Plain or Zinc Plated (Hot-Dip Galvanized optional)
Maximum Temperature: 650° F
Approvals: Complies with Federal Specification A-A-1192A (Type 26), WW-H-171-E (Type 26), ANSI/MSS SP-69 and MSS SP-58 (Type 26).
Ordering: Specify pipe size, figure number, name and finish.
Note: The acceptability of galvanized coatings at temperatures above 450°F is at the discretion of the end user.



Fig. 262: Dimensions (in) • Loads (lbs) • Weight (lbs)

Pipe Size	Max Load		Weight	Screw or Bolt Size ■	L	B	C	D	E	F
	w/ Lag Screws	w/ Bolts to Steel								
1/2	300	410	0.20	Two #18 x 2 steel wood screws or two 3/8" bolts to steel	4	1/4	2 3/4	1/2	1 1/8	1/8
3/4			0.23		4 3/8		3 1/8	1 1/16	1 7/16	
1			0.26		4 3/4		3 1/2	1 1/16	1 5/8	
1 1/4			0.36		5		3 3/4	1 1/16	2 1/8	
1 1/2			0.54		5 3/8		4 1/8	1 3/8	2 1/2	
2			0.60		6 3/8		5 1/8	1 1/4	2 3/4	
2 1/2	450	610	1.40	Two #18 x 3 steel wood screws or two 3/8" bolts to steel	6 13/16	1/2	5 9/16	1 3/4	3 5/8	1/4
3			1.60		7 5/16		6 1/16	1 7/8	4	
3 1/2			1.80		7 13/16		6 9/16	2 3/16	4 5/8	
4			1.90		8 3/8		7 1/8	2 3/8	5	

■ Screws or bolts not included

PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	