


Linked Eye Rods

Fig. 248X: Not Welded

Fig. 278X: Welded



Note:

The acceptability of galvanized coatings at temperatures above 450°F is at the discretion of the end user.

Description

Size Range

3/8" through 2 1/2"

Service

The use of linked eye rods in a hanger assembly allows universal movement of the piping without bending and possible fracture of a straight rod.

Finish

- Plain or
- Zinc Plated

Maximum Temperature

Fig. 248X: 650° F, Fig. 278X: 750° F

Ordering

Specify the size, length of each eye rod, figure number and finish.

Example

7/8" Fig. 278X linked welded eye rod consisting of:
 (L1) 7/8" Fig. 278 welded eye rod 1 ft. 2 1/2 in. long, center to end.
 (L2) 7/8" Fig. 278 welded eye rod 1 ft. 2 1/2 in. long center to end.





PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	

Linked Eye Rods

Fig. 248X: Not Welded

Fig. 278X: Welded



Dimensions (In) • Loads (Lbs)

Rod Size A	Fig. 248X 650° F	Max Load	
		650° F	750° F
3/8	240	730	572
1/2	440	1,350	1,057
5/8	705	2,160	1,692
3/4	1,050	3,230	2,530
7/8	1,470	4,480	3,508
1	1,940	5,900	4,620
1 1/4	3,120	9,500	7,440
1 1/2	4,650	13,800	10,807
1 3/4	6,380	18,600	14,566
2	8,280	24,600	19,265
2 1/4	10,900	32,300	25,295
2 1/2	13,400	39,800	31,169



asc-es.com

Building connections that last™