

Material Specifications Dimensions: ASME B16.3

Threads: NPT per ASME B1.20.1

Finish: Black

Material: ASTM A536 Grade 65-45-12

Agency Approvals: All ductile iron threaded fittings are UL/ULC Listed and FM Approved. Note: Ductile iron fittings have higher tensile strength than that of steel pipe. Therefore, over tightening can cause

damage to pipe threads which may cause leakage. Ductile

iron fittings should be tightened approximately three turns beyond hand tight, but no more than four turns.

Fig. 3201 90° Elbow





Figure 3201 90° Elbow

Maximum Nominal Size **Dimension A** Approx Wt. Each Working Pressure **A** psi (kPa) In. (mm) In. (mm) Lbs. (kg) 1 500 1.50 0.62 20 3450 38.10 0.68 11⁄4 500 1.75 0.90 3450 44.45 32 0.41 11/2 500 1.94 1.20 40 3450 49.276 0.54 2 500 2.25 1.85 50 3450 57.15 0.84

$\begin{array}{c} \leftarrow A \rightarrow \\ \uparrow \\ A \\ \downarrow \end{array}$

▲ – Working Pressure Ratings are for reference only and based on Sch. 40 pipe. For the latest UL/ULC, and FM pressure ratings versus pipe schedule, please visit asc–es.com or contact your local ASC Engineering Solutions™ Representative.



| PROJECT INFORMATION | APPROVAL STAMP |
|---------------------|-------------------|
| Project: | Approved |
| Address: | Approved as noted |
| Contractor: | Not approved |
| Engineer: | Remarks: |
| Submittal Date: | |
| Notes 1: | |
| Notes 2: | |