



Concrete Clevis Plate Fig. 49



Dimensions (In) - Load (Lbs) - Weight (Lbs)

| Rod Size A | Max Load ■ | Weight | J | B | C | D | F | G | H | R | S | T | U | W |
|------------|------------|--------|-----|-----|-----|-----|-------|-------|-----|-------|-------|-----|-------|-------|
| In. | Lbs. | Lbs. | In. | In. | In. | In. | In. | In. | In. | In. | In. | In. | In. | In. |
| 3/8 | 730 | 11.8 | | | | | | | | | | | 1/2 | |
| 1/2 | 1,350 | 11.9 | | | | | 9/16 | 3/8 | 2 | 7/8 | 1 1/4 | 1/4 | 5/8 | 2 |
| 5/8 | 2,160 | 15.7 | 1 | | 10 | 5 | | | | | | | 3/4 | |
| 3/4 | 3,230 | 16.9 | | | | | | 1/2 | | 1 1/8 | 1 7/8 | | 7/8 | 2 1/2 |
| 7/8 | 4,480 | 18.1 | | 8 | | | 11/16 | | 3 | 1 1/4 | 2 | 3/8 | 1 | |
| 1 | 5,900 | 36.9 | | | | | 13/16 | | | 1 1/2 | | 1/2 | 1 1/8 | 3 |
| 1 1/4 | 9,500 | 40.9 | | | 12 | 6 | 15/16 | 3/4 | 3 | 2 | 2 1/2 | 5/8 | 1 3/8 | 4 |
| 1 1/2 | 13,800 | 59.8 | 2 | | | | 1 1/8 | 1 | 4 | 2 1/2 | 3 | 3/4 | 1 5/8 | 5 |
| 1 3/4 | 18,600 | 93.6 | | 10 | 14 | 7 | 1 3/8 | 1 1/4 | 5 | 2 3/4 | 3 1/2 | 1/2 | 1 7/8 | |

Note:

■ Based on the rod diameter only. Rating is subject to the conditions that the concrete and anchors used are of sufficient strength to hold the load.

Material Specifications

Size Range

3/8" through 1 3/4"

Material

Carbon Steel

Finish

Plain

Hot-Dip Galvanized with Zinc Plated Fasteners

Service


Structural attachment to concrete ceiling where flexibility is desired. Concrete clevis plate is normally used in conjunction with Fig. 290 weldless eye nut, or Fig. 278 welded eye rod and anchors of sufficient strength to hold the desired load.

Ordering

Specify rod size, figure number, name and finish.

Note

Sizes 3/8" through 1" are supplied with bolt and nut. Larger sizes are supplied with pin and cotters.



| PROJECT INFORMATION | APPROVAL STAMP |
|---------------------|-------------------|
| Project: | Approved |
| Address: | Approved as noted |
| Contractor: | Not approved |
| Engineer: | Remarks: |
| Submittal Date: | |
| Notes 1: | |
| Notes 2: | |