

## Class 125 (Standard)


### Fig. 3351R Reducing 90° Elbow



For Listings / Approval Details and Limitations, visit our website at [www.asc-es.com](http://www.asc-es.com) or contact an ASC Engineered Solutions™ Sales Representative.

**Figure 3351R** Reducing 90° Elbow

Nominal Size	Maximum Working Pressure ▲	Dimensions		Approx Wt. Each
		A	B	
In. (mm)	psi (kPa)	In. (mm)	In. (mm)	Lbs. (kg)
1 x 1/2 25 x 15	300 2065	1.26 32.00	1.36 34.54	0.64 0.29
1 x 3/4 25 x 20	300 2065	1.37 34.79	1.45 36.83	0.87 0.39
1 1/4 x 1/2 32 x 15	300 2065	1.34 34.03	1.53 38.86	0.96 0.44
1 1/4 x 3/4 32 x 20	300 2065	1.45 36.83	1.62 41.14	1.13 0.51
1 1/4 x 1 32 x 25	300 2065	1.58 40.13	1.67 42.41	1.16 0.53
1 1/2 x 1/2 40 x 15	300 2065	1.41 35.81	1.66 42.16	1.17 0.53
1 1/2 x 3/4 40 x 20	300 2065	1.52 38.60	1.75 44.45	1.28 0.58
1 1/2 x 1 40 x 25	300 2065	1.65 41.91	1.80 45.72	1.51 0.68
1 1/2 x 1 1/4 40 x 32	300 2065	1.82 46.22	1.88 47.75	1.62 0.73
2 x 1/2 50 x 40	300 2065	1.49 37.84	1.88 47.75	2.00 0.91
2 x 3/4 50 x 20	300 2065	1.60 40.64	1.97 50.03	2.05 0.93
2 x 1 50 x 25	300 2065	1.73 43.94	2.02 51.30	2.10 0.95
2 x 1 1/4 50 x 32	300 2065	1.90 48.26	2.10 53.34	2.30 1.04
2 x 1 1/2 50 x 40	300 2065	2.02 51.30	2.16 54.86	2.60 1.18



### Material Specifications

**Dimensions:** ASME B16.4 Class 125

**Material:** ASTM A126

**Finish:** Black or Hot Dip Galvanized per ASTM A153 Class A

**Threads:** NPT per ASME B1.20.1

**Agency Approvals:** Fig 3351R Reducing 90° Elbow sizes 1" x 1/2" - 2" x 1 1/2" are UL/ULC Listed and FM Approved.

▲ - Working Pressure Ratings are for reference only and based on Sch. 40 pipe. For the latest UL/ULC, and FM pressure ratings versus pipe schedule, please visit [asc-es.com](http://asc-es.com) or contact your local ASC Engineering Solutions™ Representative.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	