



Two Hole Welding Beam Lug Fig. 54



Material Specifications

Size Range
1/2" through 2 1/4"

Material
Carbon Steel

Finish
Plain
Hot-Dip Galvanized

Service
For single rod suspension of Fig. 81-H, type B and C constant supports.

Ordering
Specify rod size, figure number, name, finish and "H" dimension.

Dimensions (In) - Load (Lbs) - Weight (Lbs)

Rod Size A*	Max Load	Weight "H" Dimension ▲				Rod Take Out - "H" Dimension Constant Support Frame Sizes					Pin or Bolt	K Hole	R	T	W	2W	W/2	
		1 1/2	2	3	4	1-9	10-18	19-34	35-49	50-63								
In.	Lbs.	Lbs.	Lbs.	Lbs.	Lbs.	In.	In.	In.	In.	In.	In.	In.	In.	In.	In.	In.	In.	In.
1/2	1,350	1.4	1.7	2.2	-						5/8	1 1/16						
5/8	2,160	1.4	1.6	2.2	-	1 1/2					3/4	13/16	1 1/4	3/8	2 1/2	5	1 1/4	
3/4	3,230	1.3	1.6	2.1	2.6	-		2			7/8	15/16						
1	5,900	-	2.6	3.5	4.3	-	-		3		1 1/8	1 1/4	1 1/2	1/2	3	6	1 1/2	
1 1/4	9,500	-	5.0	6.5	7.9	-	-				1 3/8	1 1/2	2	5/8	4	8	2	
1 1/2	13,800	-	-	10.7	12.8	-	-	-		4	1 5/8	1 3/4			5	10	2 1/2	
1 3/4	18,600	-	-	10.4	12.5	-	-	-			1 7/8	2		3/4				
2	24,600	-	-	-	16.0	-	-	-			2 1/4	2 3/8	3		6	12	3	
2 1/4	32,300	-	-	-	15.6	-	-	-			2 1/2	2 5/8						

Note:

Select "H" dimension applicable to constant support frame size.

▲ - Weight varies with "H" dimension.

* Rod size "A" is the assembly rod diameter. Dimension not shown on drawing.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	