

Class 125 (Standard) Fig. 3356 45° Elbow



For Listings / Approval Details and Limitations, visit our website at www.asc-es.com or contact an ASC Engineered Solutions™ Sales Representative.

Material Specifications

Dimensions: ASME B16.4 Class 125

Material: ASTM A126


Finish: Black or Hot Dip Galvanized per ASTM A153 Class A

Threads: NPT per ASME B1.20.1

Agency Approvals: Fig 3356 45° Elbow sizes 1" – 2" are UL/ULC Listed and FM Approved

Figure 3356 45° Elbow

Nominal Size	Maximum Working Pressure ▲	Dimension A	Approx Wt. Each
In. (mm)	psi (kPa)	In. (mm)	Lbs. (kg)
1 25	300 2065	1.12 28.448	0.84 0.38
1¼ 32	300 2065	1.29 32.766	1.40 0.64
1½ 40	300 2065	1.43 36.322	1.80 0.82
2 50	300 2065	1.68 42.672	2.79 1.25



▲ – Working Pressure Ratings are for reference only and based on Sch. 40 pipe. For the latest UL/ULC, and FM pressure ratings versus pipe schedule, please visit asc-es.com or contact your local ASC Engineering Solutions™ Representative.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	