

## Class 125 (Standard) Fig. 3367 Reducing Coupling



For Listings/Approval Details and Limitations, visit our website at [www.asc-es.com](http://www.asc-es.com) or contact an ASC Engineered Solutions™ Sales Representative.

### Material Specifications

**Dimensions:** ASME B16.4 Class 125

**Material:** ASTM A126


**Finish:** Black or Hot Dip Galvanized per ASTM A153 Class A

**Threads:** NPT per ASME B1.20.1

**Agency Approvals:** All cast iron threaded fittings are UL/ULC Listed and FM Approved.

**Figure 3367** Reducing Coupling

Nominal Size	Maximum Working Pressure ▲	Dimension A	Approx. Wt. Each
In. (mm)	psi (kPa)	In. (mm)	Lbs. (kg)
1 x 1/2 25 x 15	300 2065	1.70 43.18	0.62 0.28
1 x 3/4 25 x 20	300 2065	1.70 43.18	0.80 0.60



▲ – Working Pressure Ratings are for reference only and based on Sch. 40 pipe. For the latest UL/ULC, and FM pressure ratings versus pipe schedule, please visit [asc-es.com](http://asc-es.com) or contact your local ASC Engineered Solutions™ Representative.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	