

## Class 125 (Standard) Fig. 3387 Cored Plug



For Listings/Approval Details and Limitations, visit our website at [www.asc-es.com](http://www.asc-es.com) or contact an ASC Engineered Solutions™ Sales Representative.

### Material Specifications

**Dimensions:** ASME B16.4

**Material:** ASTM A126

**Finish:** Black or Hot Dip Galvanized per ASTM A153 Class A


**Threads:** NPT per ASME B1.20.1

**Agency Approvals:** All cast iron threaded fittings are UL/ULC Listed and FM Approved.

▲ Pressure - Temperature Ratings in accordance with ASME B16.4 Class 125

**Figure 3387** Cored Plug

Nominal Size	Maximum Working Pressure ▲	Dimension A	Approx Wt. Each
In. (mm)	psi (kPa)	In. (mm)	Lbs. (kg)
1/2*	300	0.94	0.10
15	2065	23.87	0.05
3/4	300	1.07	0.17
20	2065	27.17	0.08
1	300	1.25	0.28
25	2065	31.75	0.13
1 1/4	300	1.36	0.44
32	2065	34.54	0.20
1 1/2	300	1.45	0.62
40	2065	36.83	0.28
2	300	1.56	0.91
50	2065	39.62	0.41



▲ - Working Pressure Ratings are for reference only and based on Sch. 40 pipe. For the latest UL/ULC, and FM pressure ratings versus pipe schedule, please visit [asc-es.com](http://asc-es.com) or contact your local ASC Engineering Solutions™ Representative.

\*Part supplied as Solid Plug.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	