SPF Malleable Iron Threaded Fittings



Class 150 (Standard) **Fig. 3463** Unions (Brass Seat)







For Listings/Approval Details and Limitations, visit our website at www.asc-es.com or contact an ASC Engineered Solutions[™] Sales Representative.

Figure 3463 Unions (Brass Seat)

Nominal Size	Dimension A	Approx Wt. Each
In. (mm)	In. (mm)	Lbs. (kg)
1/8	1.26	0.16
6	32.00	0.07
1/4 8	1.46 37.08	0.23 0.10
³ / ₈	1.61	0.33
10	40.89	0.15
½	1.73	0.41
15	43.94	0.19
3/4	1.95	0.60
20	49.53	0.27
1	2.07	0.89
25	52.58	0.40
11/4 32	2.26 57.40	1.25 0.57
1½ 40	2.42 61.47	1.76 0.80
2	2.75	2.44
50	69.85	1.11
2½	3.23	3.52
65	82.04	1.60
3	3.50	4.34
80	88.90	1.97

Material Specifications

Dimensions:

Fittings: ASME B16.3 Unions: ASME B16.39 Bushings/Plugs: ASME B16.14

Material: ASTM A-197

Finish: Black or Hot Dip Galvanized

per ASTM A153 Class A

Threads*: NPT per ASME B1.20.1

Pressure Ratings:


Fittings: ASME B16.3 Unions: ASME B16.39

Bushings/Plugs: ASME B16.14

Pressure Testing: All malleable iron fittings are tested for through wall porosity using an air under water process.

Agency Approvals: All malleable iron fittings and unions are UL/ULC Listed and FM Approved.

*British Standard threading per BS 21 available upon request.





PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	