

Short Turn & Long Turn Elbows Fig. 703 60° Short Turn Elbow Fig. 705 45° Short Turn Elbow Fig. 706 45° Long Turn Elbow Fig. 706 45° Long Turn Elbow Fig. 707 Fig. 708

Anvil drainage fittings have sufficient sweep to allow free unobstructed flow. They are made with a shoulder of the same diameter as the inside of the pipe, in accordance with ASME B16.12, Type 1.

Thus, continuous passage is created when the pipe is screwed to the shoulder, leaving no place for solid matter to collect and clog in the pipe.

Coated drainage fittings are available upon special order request with hot dip galvanized finish (see listed sizes).

Drainage fittings with 90° bends are normally provided tapped with pitch of ¼ inch to the foot in accordance with ASME B16.12.

Note: UNPITCHED 90° fittings are POA only.

See following page for standards and specifications.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	



Short Turn & Long Turn Elbows Fig. 703, 705, 706



Standards and Specifications

Dimensions	Dimensions Material		Thread	Pressure Rating
ASME B16.12, Type 1	ASTM A126 (A)	ASTM A153	ASME B1.20.1	ASME B16.12

Note:

General Assembly of Threaded Fittings

1 Inspect both male and female components prior to assembly.

- Threads should be free from mechanical damage, dirt, chips and excess cutting oil.
- Clean or replace components as necessary.

2 Application of thread sealant

- Use a thread sealant that is fast drying, sets-up to a semi hard condition and is vibration resistant. Alternately, an anaerobic sealant may be utilized.
- Throroughly mix the thread sealant prior to application.
- Apply a thick even coat to the male threads only. Best application is achieved with a brush stiff enough to force sealant down to the root of the threads.

3 Joint Makeup

- For sizes up to and including 2" pipe, wrench tight makeup is considered three full turns past handtight. Handtight engagement for ½" through 2" thread varies from 4½ turns to 5 turns.
- For 2½" through 4" sizes, wrench tight makeup is considered two full turns past handtight. Handtight engagement for 2½" through 4" thread varies from 5½ turns to 6¾ turns.



asc-es.com


Building connections that last™

^{*} ASTM B633. Type I, SC 4, may be supplied as alternate zinc coating per applicable ASME B16 product standard.



Fig. 703 60° Short Turn Elbow






		Unit Weight		
Size	A	Black		
NPS/DN	In./mm	Lbs./kg		
11/2	13/4	2.34		
40	44	1.06		

Fig. 705 45° Short Turn Elbow






		Unit Weight				Unit Weight		
Size	A Black Galvanized	Size	Α	Black	Galvanized			
NPS/DN	In./mm	Lbs./kg	Lbs./kg	NPS/DN	In./mm	Lbs./kg	Lbs./kg	
11/2	17/16	1.71	1.71	3	213/16	6.31	6.31	
40	37	0.78	0.78	80	56	2.86	2.86	
2	1 11/16	2.79	2.79	4	25/8	11.44	11.44	
50	43	1.27	1.27	100	67	5.19	5.19	

Fig. 706 45° Long Turn Elbow





		Unit	Weight		
Size	Α	Black	Galvanized		
NPS/DN	ln./mm	Lbs./kg	Lbs./kg		
11/2	17/8	2.1	2.14		
40	48	0.97	0.97		

Note:

*Inlets tapped, pitched .25" (6mm) to the foot. Inlets of reducing fittings are always the smallest openings. See first page for pressure-temperature ratings.




asc-es.com

Building connections that last™



Short Turn & Long Turn Elbows Fig. 703, 705, 706



Shortest Offset and Face to Face With Use of Close Nipple

Size	Size Length Close			45° Short Fig. 705		45° Long Fig. 706		22½° Fig. 707		11¼° Fig. 708	
	Nipple	Α	В	Α	В	Α	В	Α	В	Α	В
NPS/DN	In./mm	In./mm	In./mm	In./mm	In./mm	In./mm	In./mm	In./mm	In./mm	In./mm	In./mm
11/2	13/4	31/2	5½	23/8	51/4	3	63/4	11/8	51/4	5/8	57/16
40	44	89	140	60	133	76	171	29	133	16	138
2	2	41/8	61/2	213/16	6 ³ / ₁₆	35/8	81/8	13/8	61/8	1 1/16	61/16
50	51	105	165	73	157	92	206	35	156	17	154
3	25/8	5%16	9	3%16	7 15/16	45/8	101/2	1 13/16	85/16	7/8	77/8
80	67	141	229	90	202	117	267	47	211	22	200
4	27/8	6½	101/2	41/4	91/2	5½	121/2	21/16	9%16	15/16	85/8
100	73	165	267	108	241	140	318	52	243	24	219



asc-es.com

Building connections that last™