

Special Clamp **Fig. 432** 



### **Description**

#### Size Range

2" through 24"

#### Material

Carbon steel

#### Finish

Plain

Hot-Dip Galvanized with Zinc Plated Bolts and Nuts

#### Maximum Temperature

Plain 750° F, Galvanized 450° F for carbon steel pipe only.

#### Service

Used with and where pipe slides cannot be welded directly to pipe or copper tube. When used with fiberglass, plastic, or aluminum pipe, a thin protective liner should be inserted between the pipe and the clamp. Clamp is designed for use with Figure 257 and Figures 436 and 439 slides and tees.

#### Ordering


Specify figure number, pipe size, name and finish.



PROJECT INFORMATION	APPROVAL STAMP
Project:	Approved
Address:	Approved as noted
Contractor:	Not approved
Engineer:	Remarks:
Submittal Date:	
Notes 1:	
Notes 2:	



# Special Clamp **Fig. 432**



## Dimensions (In) • Weight (Lbs)

Pipe Size	L	M	N	Р	Q	R Stock Size	Weight	
2	- 6 ·	5	4	- - - 10				2
21/2		5½	41/2			_	3	
3		6	5		- 1/	417	146	3
31/2		61/2	51/2	1/4	4 1/2	4½ 1/8 X 6 - - -	4	
4		7	6				4	
5		8	7				5	
6	8	95/8	81/2	2,	6	<sup>3</sup> / <sub>16</sub> X 8	12	
8		115/8	10½	3/8			15	
10		133/4	125/8				18	
12		153/4	145/8				21	
14	12	177/8	161/2	1/2			41	
16		197/8	181/2		8	1/4x 12	46	
18		217/8	201/2				52	
20		237/8	221/2	5/8			57	
24		281/8	26 <sup>7</sup> / <sub>8</sub>				67	



asc-es.com